

XWM-2424-GD-3 Wall Mount Enclosures - Wall Mount Enclosure



For more Information
please call

1-800-793-2954




Description:

24" Wall Mount Enclosure, 24" Depth with Glass Door with Lock.

Image

Image:



Physical Characteristics (Encl-CM)

Color

Color: Black

Dimensions

Length/Height: 24 inches

Depth: 24 inches

Rack Unit: 12U

Width: 21.25 inches

Load Capacity

Weight/Lbs.: 125

Material

Material: Steel

Door: Glass

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

UL Listing: UL & c-UL Listed 60950-1

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 06/01/2006

Notes (Overall)

Notes: Cabinet is symmetrical; door swing direction reversible in the field.

Product Accessories

Product Accessories:

Description	24 inches High Part Number
-------------	----------------------------

XWM-2424-GD-3 Wall Mount Enclosures - Wall Mount Enclosure

19 in. Mounting Uprights	XWM-2419
Plywood Backboard	XWM-2401
Fan Assembly	XWM-9312-1600
Mounting Screws - Bag of 50	8911-0100

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
--------	-------	-------------	-------	-------	-----------

Revision Number: 0 Revision Date: 01-28-2010

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.