BLANK DUCT PLUGS

Sealing Devices for Ducted Cable Networks

FEATURES

- All plastic construction
- Corrosion proof
- Water-tight
- Easy installation and removal
- Reusable

Blank duct plugs effectively seal conduits to reduce the cost of cable placement and maintenance in new underground construction projects and routine work. These plugs are economical because they are removable and reusable.

DUCT BANK DURABILITY

Manufactured from high-impact plastic components, combined with durable elastic gaskets, Blank plugs are corrosion proof and effective as long-term or temporary seals.

ECONOMY AND SAFETY

Both water-tight and gas-tight, Blank duct plugs prevent the flow of water and the costly sedimentation of duct banks and conduit systems while confining problems of dangerous vapors to their source.

CONVENIENCE

Each Blank plug is equipped with a rope tie device to allow the securing of pull rope to the plug's back compression plate. Installers can attach the rope to the back compression plate of the plug and store excess slack rope behind the plug within the conduit system for future use.

Ordering Information

			Duct ID Range	
Part Number	**Product Descriptor***	**Size**	**inch**	**mm**
542288	JM-BLA-07D100U	0.700	0.71 - 0.83	18.0 - 21.1
298182	JM-BLA-10D104U	1.000	0.96 - 1.16	24.4 - 29.5
187308	JM-BLA-12D148U	1.250	1.14 - 1.48	29.0 - 37.6
F64411	JM-BLA-12D163U	1.375	1.30 - 1.63	33.0 - 41.4
036620	JM-BLA-15D183U	1.500	1.49 - 1.83	37.8 - 46.5
923104	JM-BLA-20D236U	2.000	1.83 - 2.36	46.5 - 59.9
121592	JM-BLA-25D296U	2.500	2.34 - 2.96	59.4 - 75.2
162754	JM-BLA-30D346U	3.000	2.99 - 3.46	75.9 - 87.9
828822	JM-BLA-35D400U	3.500	3.45 - 3.80	86.9 - 96.5
758432	JM-BLA-35D400N	3.500	3.45 - 3.80	86.9 - 96.5
RH0166	JM-BLA-38D401-C	3.800	3.80 - 3.94	96.5 - 100.1
MP0236	JM-BLA-40D400T	4.000	3.94 - 4.17	100.1 - 105.9
293842	JM-BLA-40D402N	4.000	3.94 - 4.17	100.1 - 105.9
377850	JM-BLA-40D402U	4.000	3.94 - 4.17	100.1 - 105.9
D54832	JM-BLA-40D402U-C	4.000	3.94 - 4.17	100.1 - 105.9
F90744	JM-BLA-50D500U	5.000	4.58 - 5.02	116.3 - 127.5
934754	JM-BLA-50D535U	5.000	5.00 - 5.35	127.0 - 135.9
F76622	JM-BLA-55D590U-CR	5.500	5.51 - 5.91	140.0 - 150.1
566534	JM-BLA-60D637U	6.000	5.82 - 6.37	147.8 - 161.8
F81950	JM-BLA-70D750U-CR	7.000	7.09 - 7.55	180.1 - 191.8
885144	JM-BLA-80D816U	8.000	7.83 - 8.27	198.9 - 210.1

* T - Temporary Plug, CR- CR Rubber Gasket, C - Custom Gasket, N - Nut Version

te.com

TE Connectivity, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2014 TE Connectivity Ltd. family of companies All Rights Reserved.

315140AE 07/14 Revision

PRODUCT SHEET

Contact us

P.O. Box 1101
Minneapolis, Minnesota
USA 55440-1101

Tel: 1-800-366-3891 x73000
1-952-917-3000

Fax: 1-952-917-3237

email: bns@te.com

www.te.com/bns