CONSTRUCTION:

VARIABLE RAIL DEPTH FROM 24"-36" IN 1" INCREMENTS
BOLT TOGETHER CONSTRUCTION, SHIPS FLAT AS KIT
STEEL COMPONENTS - DURABLE TEXTURE POWDERCOAT
12 GA. C.R.S. VERTICAL UPRIGHTS
7 GA. C.R.S. HORIZONTAL FOOT BRACKET
14 GA. C.R.S. CROSS MEMBERS
14 GA. C.R.S. EXTENSION BARS
12 GA. C.R.S TOP WIDTH BRACKETS



TOE OUT MOUNTING
ISOMETRIC VIEW



TOE IN MOUNTING
ISOMETRIC VIEW



TOE OUT MOUNTING
TOP VIEW



TOE IN MOUNTING
TOP VIEW



DETAIL E



FRONT VIEW 19" EIA MTG.



EST. WEIGHT :
93.80 lbmass

THIRD ANGLE PROJECTION

INTERPRET DRAWING PER ASME Y14.5M-1994
DIMENSIONAL LIMITS APPLY AFTER APPLICATION OF FINISH
DRAWING NOT TO SCALE
TOLERANCE UNLESS OTHERWISE NOTED:
ANGULAR +/- 1°
.XXXX +/- .010
.XXX +/- .015
.XX +/- .030
.X FOR REF. ONLY
UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE IN INCHES

NOTICE:
Use of this document is subject to a confidentiality and nondisclosure agreement with Great Lakes Case & Cabinet Co., Inc. (GLCC) and may not be reproduced, disclosed or utilized in whole or in part without prior written authorization from GLCC.

PART NUMBER: VD4PM6-2436
QTY PER UNIT: 1
MATERIAL TYPE:
MATERIAL GAUGE:
FINISH:
DRAWN PCS DATE 1/27/2014
CHECKED & APP. DATE

TITLE: VARIABLE DEPTH 4 POST RACK (M6)

GREAT LAKES CASE & CABINET CO., INC.
P.O. BOX 551 EDINBORO, PA 16412
PHONE (814) 734-7303 FAX (814) 734-3907
E-MAIL glcc@greatcabinets.com

DWG NO:
REV -
SHEET: 1 OF 1