Interface and Converter Products

T&B Catalog Number: 1SVR011753R2000
UPC Number: 66201910335
Status: Active
Description:

Thermocouple converter with 24 VDC supply voltage an input signal of Type K at 0 - 1000 degrees celcius and an output signal of 0-10 volts

Features

	Plug and Work, no adjustment required
	3-way electrical isolation

Application

	For K thermocouple input and 0-10 V output applications

General

Series	CC-E
Operation-Function	Signal Converter

Dimension Information

L x W x D (inches)	2.44 x 0.89 x 2.56

Specifications

Supply Voltage (DC)	24
Sensor Input (Degrees C)	Type K at 0 - 1000
Output Signal (V)	0-10

Packaging

Package in Units	10
T&B Sold in UOM	Each
T&B Weight Per UOM	21.63 lbs. per 100

Certifications

Approvals	UL

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com