THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

SUPPLIED LABELS

19	20	21	22	23	24
13	14	15	16	17	18
7	8	9	10	11	12
1	2	3	4	5	6

PANDUIT P/N	WEIGHT
CPPL24M6BLY	6.15 LB/10 PCS (2789.6 g/10 PCS)

NOTES:
1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN [ ] ARE IN METRIC.
4. PART INCLUDES:
   - 1- METAL STAMPING
   - 4- 6 POSITION FACEPLATE WITH LABEL SLOT
   - 4- LABEL COVER
   - 4- LABEL
   - 1- SCREW KIT (INCLUDES FOUR #12-24 SCREWS)
   - 1- SCREW KIT (INCLUDES FOUR M6 SCREWS)
5. LABELS ARE PRE-NUMBERED (1-24) WITH BLANK SIDE FOR CUSTOM LABELING.





REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
3	5/12/14	JSP	REFR	MMR	REVISED AND REDRAWN, PREVIOUS REVISIONS HAVE BEEN OMITTED.	02479-056

PART NUMBER: CPPL24M6BLY

TITLE: MINI-COM 24 PORT MODULAR M6 FACEPLATE PATCH PANEL WITH LABEL/COVER

CUSTOMER DRAWING

ITEM REVISION NAME: M00806AC/00

DATASET FILE NAME: M00806AC_DC/00D

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]
.X ± .XXX ± .010 [.3]
.XX ± .03[.8] ANGLES ±
THIRD ANGLE PROJECTION

MATERIAL: PANEL: C.R.S. FACEPLATE: ABS

DRAWING NUMBER: 02479-056

DRAWN BY	DATE	CHK	SCALE	SIZE
JSP	4-16-06	MJD	NONE	A

SHT 1 OF 1

D10100DA/14