



## Audio/Video Connectors, 9-pin Screw Terminal

iSTATION™ Front-Loading  
Footprint.

RS232 Data Transmission.

Solderless - Screw Termination.

Seamless Hubbell System  
Integration.

Female to screw  
terminal.

iSTATION™  
Mounting  
Flexibility.



Easy Termination.

### SPECIFICATIONS

- ◆ **Connector:**
  - 9-pin PCB Mount
  - 9-pin Contact: Gold Plated 2μ"
  - Screw Term Contact: Brass with Nickel-plating 100μ"
- ◆ **Performance:** Serial - RS232 Data Transmission.

Hubbell's high-density 9-pin screw terminal provides an easy way to run serial data applications. The high quality connection is designed for minimal signal loss.

Providing flexibility and ease-of-use for serial applications, our DB9 screw terminal fits into a high-density 1 unit iSTATION™ module allowing for 2 additional units to be placed into a single gang faceplate for additional applications.


Create a customized multimedia workstation outlet by adding a high-density DB9 screw terminal along with Hubbell's extensive line of AV connectors, iSTATION™ modules and XCELERATOR™ jacks.

### CABLE TERMINATION

#### Cable Type:

- Standard 9-pin cable
- UTP - Unshielded Twisted Pair
- STP/ScTP/FTP

#### Screw Terminal Block Pin Out:



### CONNECTOR TERM

9-Pin D-subminiature or HD 9-pin D-sub is a common connector used for data communications. The most common application of D-sub is RS-232 serial communications. Serial communications used to transfer information between two devices using RS-232 protocol. Serial cables most commonly use the 9-pin D-subminiature, but other types of connectors can be used.

### APPLICATIONS SUPPORTED

- ▲ **Common RS232 Protocols:**
  - Transmitted Data (TxD)
  - Received Data (RxD)
  - Request To Send (RTS)
  - Clear To Send (CTS)
  - Data Terminal Ready (DTR)
  - Data Set Ready (DSR)
  - Data Carrier Detect (DCD)
  - Ring Indicator (RI)
- ▲ **Common RS232 Applications:**
  - AV Control Systems
  - White Boards
  - Asset/Device Management

### INSTALLATION TIPS

**Important:** Always allow for clearance behind connection location to ensure proper bend radius with Serial cable assemblies.

**AV Connector, 9-pin Screw Terminal**



Qty. \_\_\_\_\_ Catalog No.  
10-pack **9ST10**

**Unloaded 15-/9-pin HDMI Plates, Frames, Modules**

| Description                                                         | Catalog No.       |
|---------------------------------------------------------------------|-------------------|
| HDMI 15/9-pin Blank, Unloaded, 1 Unit, 10-pk                        | <b>IMBDS1XX</b>   |
| HDMI/15/9-pin Blank, Angled Unloaded, 1.5 Unit, 1-pk                | <b>IMBDSA15XX</b> |
| HDMI 15/9-pin AV, Panel Mount Connector, 3.5mm, Blank, 2 Unit, 1-pk | <b>IMB153X2XX</b> |
| HDMI 15/9-pin, 3.5mm, Blank, 1.5 Unit 10-pk                         | <b>IMB15315XX</b> |
| HDMI 15/p-Pin, Decorator Frame, 1-gang, 1-pk                        | <b>ISFB15XX</b>   |

**XX = Housing Colors**


"AL" = Almond; "BK" = Black; "EI" = Electric Ivory; "GY" = Gray;  
"LA" = Light Almond; "OW" = Office White; "W" = White.

**CONNECTOR DEPTH CHART****DIMENSIONS****CONNECTOR DEPTH CHART****iSTATION™ COMPATIBLE****Work Station and Cross-Connect Solutions**

- iSTATION™ Front-loading Plates
- Decorator Frames
- iSTATION™ UDX Multimedia Panels
- iFRAME® Vertical Patch Panel

**Hubbell Delivery Systems**

- Hubbell SystemOne Poke-Throughs and Floor Boxes
- Hubbell Surface Raceway, Metal and Non-Metallic
- Multi-Connect™ Wall Boxes/Conference Table Boxes

**TYPICAL APPLICATIONS**

— Patch Cords  
..... Horizontal Cable



9-pin ST Connector in Hubbell iSTATION™ face plate.

**Hubbell Premise Wiring**

HUBBELL INCORPORATED (Delaware)  
14 Lord's Hill Road • Stonington, CT 06378-0901 • (860) 535-8326 • 800-626-0005  
Fax: (860) 535-8328 • Internet site: <http://www.hubbell-premise.com>

**Worldwide Locations**

Hubbell Premise Wiring, Asia Pacific  
Hubbell Canada Inc.  
Hubbell Premise Wiring, Central America  
Hubbell Premise Wiring, China  
Hubbell Premise Wiring, Europe  
Hubbell Premise Wiring, India  
Hubbell Int'l. Inc., Korea Branch

852-2836-7131  
905-839-1138  
506-309-4158  
86-21-6374 2660  
44-01283 500500  
91-80-4022-4089  
(82 2) 2607 1363

Fax: 852-2836-7132  
Fax: 905-839-9108  
Fax: 506-260-1616  
Fax: 86-21-6374 2799  
Fax: 44-01283 500400  
Fax: 91-80-4022-4033  
Fax: (82 2) 2603 7386

Hubbell Premise Wiring, Latin America  
Hubbell de Mexico, S.A. de C.V.  
Hubbell Premise Wiring, Middle East  
Hubbell Premise Wiring, Puerto Rico  
Hubbell-Taian Co., Ltd., Taiwan  
Hubbell Premise Wiring, Venezuela

305-408-4501  
(5255) 9151-9999  
971-4-393-4192  
787-855-1075  
886-2-2522-1862  
58-212-5156482

Fax: 305-408-8201  
Fax: (5255) 9151-9989  
Fax: 971-4-393-4194  
Fax: 787-855-3265  
Fax: 886-2-2522-1872  
Fax: 58-212-6627258