



HUBBELL iStation AV Modules, Gold Speaker Posts

iSTATION™ Front-Loading Footprint.

Seamless Hubbell System Integration.

Screw-Style or Plug-In Installation for Quick and Easy Termination.

Industry Standard Banana Plug Style Connection.

High performance Gold-plated speaker post.



High impact, flame-retardant Polymer.

Quick and easy screw-on or plug-in installation.

SPECIFICATIONS

- ◆ **Connector:**
Connector Body: Brass.
Gold-plated: 2μ"
- ◆ **Material:**
Module: Flame-retardant Polymer, UL 94V-0.
- ◆ **Ring Color:** Black and Red.

Hubbell's iSTATION™ Gold speaker post modules deliver high quality audio signals throughout the home, office, classroom or to a work area. Requiring no soldering, these gold speaker post connectors install in a "snap" and provide a quick, easy screw-on or plug-in termination.

iSTATION™ Gold speaker post modules are available in 7 standard Hubbell colors and front loads into any iSTATION™ product, Hubbell Delivery System products including poke-throughs and surface raceway, or iSTATION™ UDX multimedia panels to distribute audio signals.

Create a customized multimedia work station by front-loading a iSTATION™ Gold speaker post module along with Hubbell's extensive line of AV connectors, loaded modules and XCELERATOR™ jacks.

CABLE TERMINATION

Cable Type: Stranded 14-24 AWG.

APPLICATIONS SUPPORTED

- Home theater.
- Surround sound systems.
- Entertainment systems.
- Speaker connections.

CONNECTOR TERM

Speaker Post:

Binding post is a connector commonly used on loudspeakers and audio amplifiers as well as other electrical equipment. A binding post contains a central threaded metal rod and a cap that screws down on that rod.

Banana Plug: is a single-wire (one conductor) male electrical connector used for joining wires to equipment. Commonly used on the cables connecting audio equipment, amplifiers or receivers to the loudspeakers or home sound systems.

Color-Code:

Red: + positive terminal.
Black: - negative terminal.

INSTALLATION TIPS

Important: Always allow for clearance behind connection location to ensure for proper bend radius.

Gold-plating encapsulates the connectors base metal (brass) preventing oxidation/corrosion from forming. It also has a more transparent (signal) conductive path over Nickel (3x), which is closer to the copper it's transmitting over.

iSTATION™ Speaker Post Modules

Description

Gold Speaker Post Module,
Screw Termination (R/B)

Catalog No.

IMSP1XX

XX = Color: "AL" = Almond; "BK" = Black; "EI" = Electric Ivory;
 "GY" = Gray; "LA" = Light Almond; "OW" = Office White;
 "W" = White.

Speaker Post Plugs



Catalog No. Black

SPPBK10

Catalog No. Red

SPPR10


10-pack

CONNECTOR DEPTH CHART**DIMENSIONS****iSTATION™ COMPATIBLE****Work Station and Cross-Connect Solutions**

- Front-loading Plates only
- iSTATION™ UDX Multimedia Panels only
- Multi-Connect™ Wall Boxes/Conference Table Boxes
- iFRAME® Vertical Patch Panel

Hubbell Delivery System

- Hubbell SystemOne Poke-Thrus and Floor Boxes
- Hubbell Surface Raceway, Metal and Non-Metallic

**TYPICAL APPLICATIONS**

— Patch Cords
 — Horizontal Cable



Speaker Post Module/
 AV Connector in HPW
 iSTATION™ face plate.

**Hubbell Premise Wiring**

HUBBELL INCORPORATED (Delaware)

14 Lord's Hill Road • Stonington, CT 06378-0901 • (860) 535-8326 • 800-626-0005

Fax: (860) 535-8328 • Internet site: <http://www.hubbell-premise.com>**Worldwide Locations**

Hubbell Premise Wiring, Asia Pacific
 Hubbell Canada Inc.
 Hubbell Premise Wiring, Central America
 Hubbell Premise Wiring, China
 Hubbell Premise Wiring, Europe
 Hubbell Premise Wiring, India
 Hubbell Int'l. Inc., Korea Branch

852-2836-7131
 905-839-1138
 506-309-4158
 86-21-6374 2660
 44-01283 500500
 91-80-4022-4089
 (82 2) 2607 1363

Fax: 852-2836-7132
 Fax: 905-839-9108
 Fax: 506-260-1616
 Fax: 86-21-6374 2799
 Fax: 44-01283 500400
 Fax: 91-80-4022-4033
 Fax: (82 2) 2603 7386

Hubbell Premise Wiring, Latin America
 Hubbell de Mexico, S.A. de C.V.
 Hubbell Premise Wiring, Middle East
 Hubbell Premise Wiring, Puerto Rico
 Hubbell-Taian Co., Ltd., Taiwan
 Hubbell Premise Wiring, Venezuela

305-408-4501
 (5255) 9151-9999
 971-4-393-4192
 787-855-1075
 886-2-2522-1862
 58-212-5156482

Fax: 305-408-8201
 Fax: (5255) 9151-9989
 Fax: 971-4-393-4194
 Fax: 787-855-3265
 Fax: 886-2-2522-1872
 Fax: 58-212-6627258