

AT-DINRAIL I

Media Converter DIN Rail Rack Mounting Brackets

AT-DINRAIL I

Media converter DIN Rail rack mounting brackets

Overview

The AT-DINRAIL I is a universal bracket that allows a wide range of Allied Telesis media converters and media/rate converters to be mounted onto an industry standard 35mm DIN Rail.

Saves Space and Time

This product allows network managers to have the flexibility to use the Allied Telesis media converters in standard industrial mounting installations. The DIN Rail concept allows the media converters to be mounted vertically, thus saving space.

Flexible Mounting and Security

Each AT-DINRAIL I has the ability to secure the power entry cord into the media converter, to guard against the risk of possible unwanted disconnection. In addition, each AT-DINRAIL I can be mounted in either of two directions, allowing the power inlet to the media converter to be at the top or bottom of the installation. Furthermore, each AT-DINRAIL I is physically locked into position on the DIN Rail, providing a secure and stable mounting for the media converter.

Compatible Media Converters

- AT-MC101XL
- AT-MC103XL
- AT-MC104XL
- AT-MC115XL
- AT-MC13
- AT-MC1008/GB
- AT-MC605
- AT-FS202
- AT-FS232/I
- AT-FS237S13/I
- AT-FS238B/I
- AT-FS238A/2
- AT-PC232/POE
- AT-MC102XL
- AT-MC103LH
- AT-MC104LH
- AT-MC116XL
- AT-MC1004
- AT-MC1008/SP
- AT-FS201
- AT-FS232
- AT-FS232/2
- AT-FS238A/I
- AT-FS238A/2
- AT-GS2002/SP
- AT-PC2002POE

Technical Specifications

Physical Characteristics

Dimensions 4.5cm x 14.5cm x 7.5cm
(W x D x H) 1.8in x 5.7in x 3in

Key Features

- Use with a wide range of Allied Telesis media and media/rate converters
- Compatible with 35mm DIN Rail
- Powercord anchor
- Locking mechanism
- Two way mounting

Ordering Information

AT-DINRAIL I-010

Pack containing 10 AT-DINRAIL I mounting kits

USA Headquarters | 19800 North Creek Parkway | Suite 100 | Bothell | WA 98011 | USA | T: +1 800 424 4284 | F: +1 425 481 3895
European Headquarters | Via Motta 24 | 6830 Chiasso | Switzerland | T: +41 91 69769.00 | F: +41 91 69769.11
Asia-Pacific Headquarters | 11 Tai Seng Link | Singapore | 534182 | T: +65 6383 3832 | F: +65 6383 3830

www.alliedtelesis.com

© 2009 Allied Telesis Inc. All rights reserved. Information in this document is subject to change without notice. All company names, logos, and product designs that are trademarks or registered trademarks are the property of their respective owners.

617-000337