

NEW SURFACE MOUNT SWITCH JACKS



625S2SM-xx

PART#	DESCRIPTION
625S2SM-xx	Dual line duplex switched jack, 4/4-conductor, screw terminals, filled splice connectors
COLORS (-xx):	<div style="display: flex; align-items: center;"> <div style="width: 20px; height: 20px; background-color: #f0e68c; margin-right: 5px;"></div> Ivory = (50) <div style="width: 20px; height: 20px; background-color: #c08060; margin-left: 10px; margin-right: 5px;"></div> Electrical Ivory = (52) <div style="width: 20px; height: 20px; background-color: #d3d3d3; margin-left: 10px; margin-right: 5px;"></div> White = (85) </div>

INLINE SWITCH



625ILS-52

PART#	DESCRIPTION
625ILS-52	Dual line inline switch, 12 inch flying leads, filled splice connectors
COLOR:	<div style="display: flex; align-items: center;"> <div style="width: 20px; height: 20px; background-color: #c08060; margin-right: 5px;"></div> Electrical Ivory </div>

SWITCH NID



650S2-SB-48

PART#	DESCRIPTION
650S1-48	Single line (indoor/outdoor), screw terminals, grease filled switches
650S2-48	Dual line (indoor/outdoor), screw terminals, grease filled switches
650S1-SB-48	Single line with RJ31X interface (indoor only), screw terminals, grease filled switches
650S2-SB-48	Dual line with RJ31X interface (indoor only), screw terminals, grease filled switches
COLOR:	<div style="display: flex; align-items: center;"> <div style="width: 20px; height: 20px; background-color: #808080; margin-right: 5px;"></div> Gray </div>

CONNECTING BLOCKS

41A CONNECTING BLOCKS



41A-50

- Durable plastic molding
- Hinged snap-lock cover connected to base for easy access

PART#	DESCRIPTION	WIRING
41A-50	4 terminating posts, hinged snap-lock cover	USOC
41B-50	6 terminating posts, hinged snap-lock cover	USOC
COLOR:	<div style="display: flex; align-items: center;"> <div style="width: 20px; height: 20px; background-color: #f0e68c; margin-right: 5px;"></div> Ivory </div>	

42A CONNECTING BLOCKS



42A-50

- Separate base and cover
- Cover includes captive retaining screw to securely fasten to the assembly
- Plastic base contains molded brass inserts

PART#	DESCRIPTION	WIRING
42A-50	4 terminating posts, includes screw-on cover	USOC
020031-50	4 terminating posts, block only	USOC
COLOR:	<div style="display: flex; align-items: center;"> <div style="width: 20px; height: 20px; background-color: #f0e68c; margin-right: 5px;"></div> Ivory </div>	