On Line Catalog



BURNDY Catalog Number	BIBD6003
UPC Number	781810225295
Description	600-3 TWO SIDE UNITAP
Status	Active

Web Use
BURNDY Product Line

Dimensional	
Width (in)	3.00
Hex Size (Key)	3/8
Length (in)	3.77
Height (in)	2.75
Electrical	
Min Voltage Rating	600
General	
Number of Ports	3
Number of Screws	3
Product Description	Aluminum Multiple Tap Connector, Clear Insulated, 3 Port, 2 Sided Entry, 4 AWG-600 kcmil, Al/Cu Rated
Conductor(s)	
Aluminum Size (Range)	4 AWG-600 kcmil
Copper Solid Size (Range)	N/A
Copper Stranded (Range)	4 AWG-600 kcmil
Physical	
Type of Hardware	Aluminum
Type of Plating	Unplated
Insulation Type	Plastisol
Plated (Yes or No)	N
Product Material	Aluminum
Approvals / Certifications	
Rated for Direct Burial	N
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
Manchester NH03109

Hours: 8.00 AM - 5.00 PM
Monday - Friday
Phone: 000-346-4175