On Line Catalog

BURNDY Catalog Number	BIBS7504
UPC Number	781810233078
Description	750-2 1-SIDED-4 UNITAP
Status	Active

Web Use
BURNDY Product Line

Dimensional	
Width (in)	2.70
Hex Size (Key)	3/8
Length (in)	5.38
Height (in)	3.00
Electrical	
Min Voltage Rating	600
General	
Number of Ports	4
Number of Screws	4
Product Description	Aluminum Multiple Tap Connector, Clear Insulated, 4 Port, 1 Sided Entry, 2 AWG-750 kcmil, Al/Cu Rated
Conductor(s)	
Aluminum Size (Range)	2 AWG-750 kcmil
Copper Solid Size (Range)	N/A
Copper Stranded (Range)	2 AWG-750 kcmil
Physical	
Type of Hardware	Aluminum
Type of Plating	Unplated
Insulation Type	Plastisol
Plated (Yes or No)	N
Product Material	Aluminum
Approvals / Certifications	
Rated for Direct Burial	N
UL Listed	N
CSA Certified	N
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
Manchester NH03109

Hours: 8.00 AM - 5.00 PM
Monday - Friday
Phone: 000-346-4175