On Line Catalog

BURNDY Catalog Number	YA4CL390
UPC Number	781810019917
Description	4 STR CU 1-H SHORT 90DEG
Status	Active

Web Use
BURNDY Product Line

Dimensional	
Tongue Angle	90 Degree
Length (in)	0.96
Tongue Type	Standard
Barrell Style	Chamfered,Skived
Bolt Hole Size (in)	0.33
Barrel Type	Standard
Thickness	0.09
B Length (in)	0.81
Pad Width (in)	0.50
Strip Length	7/8
General	
Number of Holes	1
Product Description	Cu code conductor standard barrel, Single hole/W/ insp window, 5/16" stud, Tin plated,Grey,8 index
Conductor(s)	
Flex (Class G) Size - Range	N/A
Flex (Class H) Size - Range	N/A
Flex (Class I) Size - Range	N/A
Copper Solid Size (Range)	N/A
DLO Size (Range)	N/A
Copper Stranded (Range)	4 AWG
Physical	
Type of Plating	Tin - Electro Plated
Bolt Hole Size	5/16
Color Code	Gray
Plated (Yes or No)	Y
Index Number	8,346
Product Material	Copper
Approvals / Certifications	
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL467

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
Manchester NH03109

Hours: 8.00 AM - 5.00 PM
Monday - Friday
Phone: 000-346-4175