



HUBBELL  
**iStation**

## Audio Video Connectors, RCA, Feed-Thru

Seamless Hubbell System  
Integration.

Universal Keystone Design fits  
into all Hubbell Products.

7 Different Insulator Colors.

High Quality Gold Plating.

High performance,  
Gold-plated RCA  
connector.



Deliver Composite,  
Component or  
Digital Signals.

High-impact, flame-  
retardant polymer.

### SPECIFICATIONS

- ◆ **Female Connector:**
  - Body: Brass
  - Gold-Plated: 2μ"
- ◆ **Performance:**
  - Impedance: 75 Ohms
  - Mating Cycles: 500+
- ◆ **Material:**
  - Housing: flame retardant polymer rated UL 94V-0.
- ◆ **Insulator Color:** Black, Blue, Green, Orange, Red, White, and Yellow.

Hubbell's RCA gold feed-thru connectors deliver high quality A/V signals to work areas and/or transmitting/receiving devices. Requiring no soldering, these RCA connectors install with a snap and provide a quick easy "push-on" termination.

These RCA-Connectors are available with seven standard insulator colors housed in seven Hubbell colors, accommodating all common A/V applications. RCA-Connectors mount into all **iSTATION™** faceplates, surface mount boxes, modules, frames, Hubbell Delivery System products including poke-throughs and surface raceway, and **iSTATION™** UDX multimedia panels.

Create a customized multimedia workstation by adding a RCA gold feed-thru connector along with Hubbell's extensive line of AV connectors, loaded modules and **XCELERATOR™** jacks.

### CONNECTOR TERM

**RCA Connector** - The standard connector used in line-level consumer and studio sound equipment. RCA connectors supply unbalanced signal and are used in almost all systems and between almost all audio/video components. They are used for inter-connecting Composite, Component and Digital coaxial audio video signals.

### APPLICATIONS SUPPORTED

- ▲ Composite/component audio/video distribution.
- ▲ TV, CCTV, CATV and satellite.
- ▲ Home theater and entertainment systems.
- ▲ Cameras, camcorders and projectors.
- ▲ Security and surveillance systems.

### CABLE TERMINATION

- Cable Type:**
- Coax 75 Ohm - RG6, RG59, Mini-Coax, RCA patch cords.

### INSTALLATION TIPS

**Important:** Always allow for clearance behind connection location to ensure for proper bend radius.

**Termination:** Connection is a "push on" RCA connector (patch cord).

**Gold Plating:** Gold plating encapsulates the connector's base metal (brass) preventing oxidation/corrosion from forming. It also has a more transparent (increased signal transfer) conductive path over nickel (3x).

**AV Connector, RCA Feed-Thru**

Sold in carton increments only. Carton contains - 25 keystone connectors (individually bagged).



Housing/Insulator Color	Plating	Catalog No.
See below	Gold	<b>SFRCXXFFXX</b>
Housing: Office White	Nickel	<b>SFRCXXFF</b>


**XX** = Housing Color: "AL" = Almond; "BK" = Black; "EI" = Electric Ivory; "GY" = Gray; "LA" = Light Almond; "OW" = Office White; "W" = White.

**XX** = Insulator Color: "BK" = Black; "B" = Blue; "GN" = Green; "OR" = Orange; "R" = Red; "W" = White; "Y" = Yellow.


**RCA INSULATOR COLOR: APPLICATIONS**

Color	Audio	Video
Red	Right Signal	Component - Red (Pr/Cr)
White	Left Signal	
Yellow		Composite
Blue		Component - Blue (Pb/Cb)
Green		Component - Green (Y)
Black	Mono/Right	
Orange	Digital (S/PDIF)	Digital (S/PDIF)

**CONNECTOR DEPTH CHART**



**DIMENSIONS**



**iSTATION™ COMPATIBLE**

**Work Station and Cross-Connect Solutions**

- Front and Rear-loading Plates
- Duplex and Decorator Frames
- ISM Surface Mount Boxes
- UDX Multimedia Panels (except 1U-48)
- NETSELECT® Residential Network Solution
- iFRAME® Vertical Patch Panel




**Hubbell Delivery System**

- Hubbell SystemOne Poke-Thrus and Floor Boxes
- Hubbell Surface Raceway, Metal and Non-Metallic
- Multi-Connect™ Wall Boxes/Conference Table Boxes
- Power Poles



**TYPICAL APPLICATION**



— Patch Cords  
— Horizontal Cable

RCA AV module/  
connector in a Hubbell  
iSTATION™ face plate.



**Hubbell Premise Wiring**

HUBBELL INCORPORATED (Delaware)  
14 Lord's Hill Road • Stonington, CT 06378-0901 • (860) 535-8326 • 800-626-0005  
Fax: (860) 535-8328 • Internet site: <http://www.hubbell-premise.com>

**Worldwide Locations**

Hubbell Premise Wiring, Asia Pacific  
Hubbell Canada Inc.  
Hubbell Premise Wiring, Central America  
Hubbell Premise Wiring, China  
Hubbell Premise Wiring, Europe  
Hubbell Premise Wiring, India  
Hubbell Int'l. Inc., Korea Branch

852-2836-7131  
905-839-1138  
506-309-4158  
86-21-6374 2660  
44-01283 500500  
91-80-4022-4089  
(82 2) 2607 1363

Fax: 852-2836-7132  
Fax: 905-839-9108  
Fax: 506-260-1616  
Fax: 86-21-6374 2799  
Fax: 44-01283 500400  
Fax: 91-80-4022-4033  
Fax: (82 2) 2603 7386

Hubbell Premise Wiring, Latin America  
Hubbell de Mexico, S.A. de C.V.  
Hubbell Premise Wiring, Middle East  
Hubbell Premise Wiring, Puerto Rico  
Hubbell-Taian Co., Ltd., Taiwan  
Hubbell Premise Wiring, Venezuela

305-408-4501  
(5255) 9151-9999  
971-4-393-4192  
787-855-1075  
886-2-2522-1862  
58-212-5156482

Fax: 305-408-8201  
Fax: (5255) 9151-9989  
Fax: 971-4-393-4194  
Fax: 787-855-3265  
Fax: 886-2-2522-1872  
Fax: 58-212-6627258