


➔ WALL MOUNT JACK ASSEMBLIES

- Versatile mounting options
- Can be mounted on a standard outlet box for pre-wired installations, or attached directly to the wall
- Entire terminal block is enclosed in a plastic wrapper to eliminate corrosion and shorting out due to condensation or incidental moisture

PLASTIC : WITHOUT MOUNTING LUGS



630AB4-xx



630ABS6-xx

PART#	DESCRIPTION	WIRING
630AB4-xx	4-conductor, quick-connect terminals, no mounting lugs	USOC
630AB6-xx	6-conductor, quick-connect terminals, no mounting lugs	USOC

Note: Quick Connect Terminals require use of 797A installation tool (see page 35).


PART#	DESCRIPTION	WIRING
630ABS4-xx	4-conductor, screw terminals, no mounting lugs	USOC
630ABS6-xx	6-conductor, screw terminals, no mounting lugs	USOC

COLORS (-xx):  Ash = (44)  Ivory = (50)


PLASTIC : WITH MOUNTING LUGS



- Packaged with mounting lugs for use with modular wall telephones or plastic inserts for desk applications



630ABC4-xx




630AC4-xx

PART#	DESCRIPTION	WIRING
630ABC4-xx	4-conductor, quick-connect terminals, includes 797A termination tool	USOC
630ABC6-xx	6-conductor, quick-connect terminals, includes 797A termination tool	USOC

PART#	DESCRIPTION	CORROSHIELD	WIRING
630AC4-xx	4-conductor, screw terminals		USOC
630AC4-xxRC	4-conductor, screw terminals	CorroShield	USOC
630AC4NS-xxRC	4-conductor, filled splice connectors, riser plate	CorroShield	USOC
630AC6-xx	6-conductor, screw terminals		USOC
630AC6NS-50RC	6-conductor, filled splice connectors, riser plate	CorroShield	USOC





COLORS (-xx):  Ash = (44)  Ivory = (50)  Electrical Ivory = (52)



630AP4-xx

➔ **IN DEPTH:** 630AP wall plates feature an all plastic wall plate with a snap-on cover

PART#	DESCRIPTION	CORROSHIELD	WIRING
630AP4-xx	4-conductor, screw terminals		USOC
630AP4NS-50RC	4-conductor, filled splice connectors	CorroShield	USOC
630AP6-xx	6-conductor, screw terminals		USOC
630AP6NS-50RC	6-conductor, filled splice connectors	CorroShield	USOC
630AP8-xx	8-conductor, screw terminals		USOC

COLORS (-xx):  Ash = (44)  Ivory = (50)  Elect. Ivory = (52)  White = (85)