


Communication & Low Voltage



- Permits fast and easy installation on beam flanges.
- Qwik-Latch™ cable retainer included with each hook.
- Static Load Capacity: 30 Lbs.
- Finish: Pre-galvanized

Cable To Beam Fasteners



Communication & Low Voltage


UPC/Part Number	Catalog Number	Hook Size	Flange Thickness	Box Qty.
782051 28067	BCH12-E-2-4	3/4"	1/8" to 1/4"	50
782051 28072	BCH12-E-5-8	3/4"	5/16" to 1/2"	50
782051 28073	BCH12-E-9-12	3/4"	9/16" to 3/4"	50
781011 04803	BCH21-E-2-4	15/16"	1/8" to 1/4"	50
781011 04805	BCH21-E-5-8	15/16"	5/16" to 1/2"	50
781011 04807	BCH21-E-9-12	15/16"	9/16" to 3/4"	50
781011 04825	BCH32-E-2-4	2"	1/8" to 1/4"	25
781011 04827	BCH32-E-5-8	2"	5/16" to 1/2"	25
781011 04829	BCH32-E-9-12	2"	9/16" to 3/4"	25

(See pages 234-235 for technical data.)

Read safety/installation instruction sheets in packages before use.

Communication & Low Voltage

- Permits fast and easy installation on beam flanges.
- Qwik-Latch™ cable retainer included with each hook.
- Static Load Capacity: 30 Lbs.
- Finish: Pre-galvanized



Cable To Beam Fasteners



Allows
360°
Rotation




UPC/Part Number	Catalog Number	Hook Size	Flange Thickness	Box Qty.
782051 28062	BCH12-U-2-4	3/4"	1/8" to 1/4"	50
782051 28064	BCH12-U-5-8	3/4"	5/16" to 1/2"	50
782051 28066	BCH12-U-9-12	3/4"	9/16" to 3/4"	50
781011 04809	BCH21-U-2-4	15/16"	1/8" to 1/4"	50
781011 04811	BCH21-U-5-8	15/16"	5/16" to 1/2"	50
781011 04813	BCH21-U-9-12	15/16"	9/16" to 3/4"	50
781011 04831	BCH32-U-2-4	2"	1/8" to 1/4"	50
781011 04833	BCH32-U-5-8	2"	5/16" to 1/2"	50
781011 04835	BCH32-U-9-12	2"	9/16" to 3/4"	50
781011 04864	BCH64-U-2-4	4"	1/8" to 1/4"	25
781011 04865	BCH64-U-5-8	4"	5/16" to 1/2"	25
781011 04866	BCH64-U-9-12	4"	9/16" to 3/4"	25

(See pages 234-235 for technical data.)

Read safety/installation instruction sheets in packages before use.

Communication & Low Voltage




- 360° rotation allows cable to run in any direction.
- Qwik-Latch™ cable retainer included with each hook.
- Static Load Capacity: 30 Lbs.
- Finish: Pre-galvanized

Cable To Beam Fasteners



Communication & Low Voltage

UPC/Part Number	Catalog Number	Hook Size	Flange Thickness	Box Qty.
782051 28077	BCH12-C442	3/4"	1/8" to 5/8"	50
781011 04823	BCH21-C442	15/16"	1/8" to 5/8"	50
781011 04845	BCH32-C442	2"	1/8" to 5/8"	50
781011 04868	BCH64-C442	4"	1/8" to 5/8"	25



- 360° rotation allows cable to run in any direction.
- Qwik-Latch cable retainer included with each hook.
- Static Load Capacity: 30 Lbs.
- Finish: Pre-galvanized

Cable To Beam Fasteners




UPC/Part Number	Catalog Number	Hook Size	Flange Thickness	Box Qty.
782051 41850	BCH12-C442A	3/4"	1/8" to 5/8"	50
782051 41851	BCH21-C442A	15/16"	1/8" to 5/8"	50
782051 41852	BCH32-C442A	2"	1/8" to 5/8"	50
782051 41853	BCH64-C442A	4"	1/8" to 5/8"	25

(See pages 234-235 for technical data.)

Read safety/installation instruction sheets in packages before use.

Communication & Low Voltage

- 360° rotation allows cable to run in any direction.
- Qwik-Latch™ cable retainer included with each hook.
- Static Load Capacity: 30 Lbs.
- Finish: Pre-galvanized




Cable To Beam Fasteners



Communication & Low Voltage

UPC/Part Number	Catalog Number	Hook Size	Flange Thickness	Box Qty.
782051 28074	BCH12-C2	3/4"	thru 1/2"	50
781011 04821	BCH21-C2	15/16"	thru 1/2"	50
781011 04843	BCH32-C2	2"	thru 1/2"	50
781011 04867	BCH64-C2	4"	thru 1/2"	25

- Qwik-Latch cable retainer included with each hook.
- Static Load Capacity: 30 Lbs.
- Finish: Pre-galvanized



Cable To Beam Fasteners



UPC/Part Number	Catalog Number	Hook Size	Flange Thickness	Box Qty.
782051 41303	BCH12-C1	3/4"	thru 1/2"	50
781011 95578	BCH21-C1	15/16"	thru 1/2"	50
781011 95560	BCH32-C1	2"	thru 1/2"	50
782051 41304	BCH64-C1	4"	thru 1/2"	25

(See pages 234-235 for technical data.)

Read safety/installation instruction sheets in packages before use.