THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

1. SEE SHEET 2 FOR PRODUCT DESCRIPTIONS AND TECHNICAL SPECIFICATIONS.
2. SEE CURRENT CATALOG FOR PATCH CORD/PIGTAIL LENGTHS AND PACKAGE QUANTITY.
3. FOR LENGTHS OTHER THAN THOSE LISTED IN CATALOG, CONTACT YOUR PANDUIT SALES PERSON.
4. TESTED TO EIA/TIA 568-B.3.
5. PATCH CORD ROUTING CONFIGURATION A TO B.
6. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.



REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH
R	10-25-07	MC		RELEASED TO PRODUCTION	02779-54			

FIBER OPTIC
DUPLEX KEYED LC PIGTAIL
CUSTOMER DRAWING

PANDUIT™ CORP.
TINLEY PARK, ILL 60477

THIRD ANGLE PROJECTION

ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED.
DIMENSIONAL TOLERANCES ARE:
(.X) (.XXX)±.010 [0.3]
(.XX)±.03 [0.8] ANGLES

DRAWN BY: MC
DATE: 10-01-07
CHK'D:
REVIEW DRAWING NUMBERS

DRAWING FILENAME: M02779CT_DC_00A.prt
SCALE: NONE
PART NO.: SEE TABLE, SHT. 2
DRAWING NO.: 02779-54 (SHT. 1 of 2)
SIZE: A

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

DUPLEX KEYED LC FIBER OPTIC PIGTAIL

PANDUIT PART NO.	CABLE				KEYED LC CONNECTOR		
	FIBER TYPE	RATING	COUNT	COLOR	MAX. IL	MIN. RL	KEY/COLOR
F5PE10A-NM** F5PE10B-NM** F5PE10C-NM** F5PE10D-NM** F5PE10E-NM** F5PE10F-NM**	50/125um OM2	PLENUM (OFNP)	DUPLEX 1.6mm ZIPCORD	ORANGE	0.30dB	20dB	A/BLACK B/RED C/GREEN D/YELLOW E/ORANGE F/DK.BLUE
F6PE10A-NM** F6PE10B-NM** F6PE10C-NM** F6PE10D-NM** F6PE10E-NM** F6PE10F-NM**	62.5/125um OM1	PLENUM (OFNP)	DUPLEX 1.6mm ZIPCORD	ORANGE	0.30dB	20dB	A/BLACK B/RED C/GREEN D/YELLOW E/ORANGE F/DK.BLUE
FXPE10A-NM** FXPE10B-NM** FXPE10C-NM** FXPE10D-NM** FXPE10E-NM** FXPE10F-NM**	10 GbE 50/125um OM3	PLENUM (OFNP)	DUPLEX 1.6mm ZIPCORD	AQUA	0.30dB	26dB	A/BLACK B/RED C/GREEN D/YELLOW E/ORANGE F/DK.BLUE
F9PE10A-NM** F9PE10B-NM** F9PE10C-NM** F9PE10D-NM** F9PE10E-NM** F9PE10F-NM**	9/125um OS1	PLENUM (OFNP)	DUPLEX 1.6mm ZIPCORD	YELLOW	0.35dB	55dB	A/BLACK B/RED C/GREEN D/YELLOW E/ORANGE F/DK.BLUE

** - DENOTES PATCH CORD LENGTH, WHERE M = METERS AND F = FEET

REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH
R	10-25-07	MC		RELEASED TO PRODUCTION	02779-54			

FIBER OPTIC
DUPLEX KEYED LC PIGTAIL
CUSTOMER DRAWING

PANDUIT™ CORP.
TINLEY PARK, ILL 60477

THIRD ANGLE PROJECTION

ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED.
DIMENSIONAL TOLERANCES ARE:
(.X) (.XXX)±.010 [0.3]
(.XX)±.03 [0.8] ANGLES

DRAWN BY: MC
DATE: 10-01-07
CHK'D:
REVIEW DRAWING NUMBERS: AS NOTED

DRAWING FILENAME: M02779CT_DC_00A.prt
SCALE: NONE
PART NO.: SEE TABLE
DRAWING NO.: 02779-54 (SHT. 2 of 2)
SIZE: A