Product Specifications

COMMSCOPE

This specification is OBSOLETE

760001776 | 1100-GS3-1U

GigaSPEED XL® 1100GS3 Category 6 U/UTP 1U Panel Kit

OBSOLETE

This product was discontinued on: December 1, 2015

Replaced By:

760206896 1100-U-GS3-KIT-1U	1100 GS3 PANEL KIT - 1U

Dimensions

Depth	40.64 mm | 1.60 in
Height	44.45 mm | 1.75 in
Width	482.60 mm | 19.00 in

Electrical Specifications

Current Rating	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1500 Vac @ 60 Hz
Dielectric Withstand Voltage, RMS, contact-to-contact	1000 Vac @ 60 Hz
Insulation Resistance, minimum	500 MOhm

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	cUL | UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Intelligence Type	Passive
Cable Type	U/UTP (unshielded)
Product Type	Panel
Brand	GigaSPEED XL® | SYSTIMAX®
Color	Black
Rack Type	EIA 19 in

Mechanical Specifications

Panel Style	Straight
Conductor Gauge, solid	22 AWG | 24 AWG

©2016 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope.
All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: January 16, 2016

Product Specifications

760001776 | 1100-GS3-1U

Conductor Gauge, stranded	22 AWG	24 AWG
Conductor Type	Solid	Stranded (7 strands)
Material Type	Powder-coated steel

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

©2016 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope.
All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: January 16, 2016