Thomas&Betts

Rigid/IMC Conduit Bodies, Covers & Gaskets

T&B Catalog Number: LR300M

UPC Number: 78621096189

Status: Active

Description:

Series 35 Right Side Opening 3 Inch Conduit Body, Body Material Malleable Iron, Finish Zinc Plating with an Aluminum, Acrylic Coating for Use with Rigid/IMC Conduit



Features

	Zinc-plated iron construction with aluminum acrylic coating provides durability, impact resistance and corrosion resistance.
	Features tapered, threaded NPT hubs.
	Covers available in iron or stamped steel, both zinc-plated and supplied with stainless steel captive screws.
	Suitable for use in concrete.

Application

	To connect conduit sections
	Serve as pulling outlets during conductor installation
	Provide easy access for splices in brand conductors
	Make 90 degree bends in conduit runs
	Act as mounting outlets for wiring devices and lighting fixtures
	Provide access to conductors for maintenance and future system changes

General

Trade Size (inches)	3
Material	Malleable Iron
Finish	Zinc Plating with Aluminum Acrylic Coating
Volume (cu.in.)	173.0
Conduit Body Shape	LR

Dimension Information

Dimension A (inches)	13 7/8
Dimension B (inches)	4 3/4
Dimension C (inches)	5 7/8

Packaging

Package in Units	1
T&B Sold in UOM	Each
T&B Weight Per UOM	13.9 lbs. Each

Application Support

T&B Sales Drawings	wsd-000256
Product Brochure-BlueKote Universal Conduit Elbow	Available on Website
Form 7-Form 8 & Series 35 Conduit Body Fill	Available on Website
Product Brochure-Stainless Steel Form 8 Conduit Outlet Bodies	Available on Website

Certifications

RoHS Compliance	Yes

Certifications

File Nbr:

E 2969

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com