THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



SEE SHEET 2 FOR SPECIFICATIONS

FILE LOCATION: TEAMCENTER

REV	DATE	BY	CHK'D	DESCRIPTION	ECN	-R	CUST	SUP
04	2-08-16	BLR	ABJ	UPD LABEL ADDRESS	4908	--	JADE	
03	11-24-14	BLR	ABJ	UPD BRANDING, LABEL GRAPHIC	4782	--	JADE	
02	7-22-05	BLR	ABJ	REDRAWN W/CHANGES	4158	--	DLWE	

PANDUIT CORP. TINLEY PARK, ILLINOIS

PTS CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
(.x) ± --- (.xxx) ± ---
(.xx) ± --- ANGLES ± ---

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY: BLR

MATL:

SHEET 1 OF 2

SCALE NONE

DATE: 3-04-04

DRAWING NO. WB24652A01

DWG A

CHK'D: ABJ

SIZE

NOTES UNLESS OTHERWISE SPECIFIED:
PANDUIT TOOL NUMBER PTS INSTALLS: SM, M, I, AND S CABLE TIE CROSS-SECTIONS. THIS PNEUMATIC TOOL TIGHTENS CABLE TIES AND CUTS OFF EXCESS PORTION WHEN PRESET IS ATTAINED.

CABLE TIE CROSS-SECTION CODE:
SM = SUBMINIATURE, M = MINIATURE,
I = INTERMEDIATE, S = STANDARD

TOOL WEIGHT = 17.3 OZ. (490 GRAMS)

PNEUMATIC REQUIREMENTS = 70 – 90 PSIG
FILTERED NON-LUBRICATED AIR AND EXTERNAL PNEUMATIC HOSE

REFERENCE:
KGTSBLD – BLADE REPLACEMENT KIT
KPTSTL - TENSION LOCKING KIT
PPH10 – EXTERNAL PNEUMATIC HOSE: 1/8” NPT FEMALE QUICK DISCONNECT SOCKET, AND 1/8” NPT MALE QUICK DISCONNECT FITTING.
PHCA – EXTERNAL PNEUMATIC HOSE: 1/8” NPT FEMALE QUICK DISCONNECT SOCKET, AND ¼” NPT MALE QUICK DISCONNECT FITTING.
PL289N1 – FILTER/REGULATOR
WB24468D01 – BLADE GUARD HOUSING

DIMENSIONS SHOWN IN (PARENTHESES) ARE METRIC:

A = 2.37	(60.19)	TRIGGER SPAN
B = 9.42	(239.27)	OVERALL LENGTH
C = 6.38	(162.05)	OVERALL HEIGHT
D = .060/.066	(1.52/1.68)	BLADE GUARD SLOT WIDTH
E = 0.74	(18.79)	BLADE GUARD HEIGHT
F = 0.55	(13.97)	BLADE GUARD WIDTH
G = 0.90	(22.86)	SELECTOR KNOB
H = 1.34	(34.04)	TOOL WIDTH

PNEUMATIC HOOK UP:
ATTACH FEMALE QUICK DISCONNECT SOCKET END OF PNEUMATIC HOSE TO MALE QUICK DISCONNECT FITTING AT END OF PTS TOOL.



SEE SHEET 1 FOR PICTORAL

REV	DATE	BY	CHK’D	DESCRIPTION	ECN	-R	CUST	SUP

SEE SHEET 1 FOR DRAWING REVISION & RELATED INFORMATION

PANDUIT CORP. TINLEY PARK, ILLINOIS

PTS CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
(.x) ± --- (.xxx) ± ---
(.xx) ± --- ANGLES ± ---

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY: -----
DATE: -----
CHK’D: -----

MATL:
SHEET 2 OF 2

SCALE NONE
DRAWING NO. WB24652A01
DWG SIZE A