THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

H

K

PANDUIT PART NUMBER	LENGTH	WEIGHT	WEIGHT/LENGTH
FR6X4**2 (SEE NOTE 1)	78.74 IN ±.18 IN (2000.0mm ±4.6mm)	9.71 LB (4404g)	1.48 LB/FT (22.0g/cm)
FR6X4**6 (SEE NOTE 1)	72.00 IN ±.18 IN (1828.8mm ±4.6mm)	8.88 LB (4028g)	1.48 LB/FT (22.0g/cm)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. DIMENSIONS IN PARENTHESES ARE IN METRIC.



ENG. REF.: D37185CC_DC_FR6X4_01.prt

CAD FILENAME/LAYERS J FR6X4.pdf

PANDUIT CORP TINLEY PARK, ILLINOIS

FIBERRUNNER 6x4 CHANNEL (FR6X4**2, FR6X4**6)

I

CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
(.X) ± (.XXX) ±
(.XX) ±.03 (0.8) ANGLES ±

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

REV	DATE	BY	CHK	DESCRIPTION	ECN	-	R	CUST	SUP	GMBH
-	--------	---	---	K. REVISED ENTIRE CHART J. REVISED CAD FILENAME	--------		--	--		
5	7-21-06	DTP	RN	I. REVISED DRAWING TITLE H. REVISED AND REDRAWN	37185-82		RN	RN		

DRAWN BY JHNU
DATE 5-11-00
CHK'D NEY
MAT'L: PVC
SCALE NONE
DRAWING NO. 37185-82
DWG A
SIZE