Product Specifications

COMMSCOPE

4-2055578-0

MPOptimate® Trunk Cable, 24 fiber, duplex, OM4, 40 m, aqua

Body Features

Cable Color	Aqua

Configuration Features

Number of Fibers	24
Number of Connectors (End A)	2
Number of Connectors (End B)	2
Exit Angle to Exit Angle	180° to 180°

Dimensions

Assembly Length	40.00 m | 131.23 ft
Cable Outer Diameter	.315 in | 8 mm

Industry Standards

Flammability Rating	LSZH

Product Availability

Region	Australia/New Zealand | EMEA

Product Type Features

Product Type	Trunk cable
System	MPOptimate®
Connector Type (End A)	MPO
Connector Type (End B)	MPO
Fiber Type	OM4
Fiber Diameter	50/125 µm
Optical Mode	Multimode
Polarity	Straight

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant

* Footnotes

Assembly Length	Assembly length includes the breakout lengths

©2017 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope.
All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: February 17, 2017