126-01003

HellermannTyton

Article Number: 126-01003

Description: Arrowhead Push-Mount Cable Tie, 8.3"L, 50lb, Panel Thickness .25"– .28", PA66HS, Black, 100/pkg

Base Data		
	Local Order Number	T50RSF0C2
	Type	T50RSF(U)
	Color	Black (BK)
	Features and benefits	• Push Mount design creates quick and easy mounting for installers. • Push mount style creates low insertion and high extraction force. • Ties "clicks" into place upon final installation signaling installer insertion is complete.
	Quantity Per	bag
	Product Description	Push Mount Ties provide a one piece, all plastic tie for quick and simple cable mounting.
	Short Description	Arrowhead Push-Mount Cable Tie, 8.3"L, 50lb, Panel Thickness .25"– .28", PA66HS, Black, 100/pkg
Product Dimensions		
	Minimum Tensile Strength (Imperial)	50.0lbs
	Minimum Tensile Strength (Metric)	225N
	Length L (Imperial)	8.3"
	Length L (Metric)	210.0mm
	Fixation Method	Arrowhead
	Identification Plate Position	none
	Releasable Closure	No
	Tie Closure	plastic pawl
	Variant	Inside Serrated
	Width W (Imperial)	0.19"
	Width W (Metric)	4.7mm
	Height H (Imperial)	.30"
	Height H (Metric)	7.50mm
	Bundle Diameter Min. (Imperial)	0.06"
	Bundle Diameter Min. (Metric)	1.6mm

Product Dimensions	Bundle Diameter Max. (Imperial)	1.7"
	Bundle Diameter Max. (Metric)	44.0mm
	Panel Thickness Max. (Imperial)	0.14"
	Panel Thickness Max. (Metric)	3.56mm
	Panel Thickness Min. (Imperial)	0.04"
	Panel Thickness Min. (Metric)	1.00mm
	Mounting Hole Diameter D (Imperial)	0.25 - 0.28"
	Mounting Hole Diameter D (Metric)	6.4 - 7.1 mm
	Mounting Hole Diameter D Min. (Imperial)	0.25"
	Mounting Hole Diameter D Max. (Imperial)	0.28"
	Thickness T (Imperial)	0.05"
	Thickness T (Metric)	1.2mm
Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66HS
	Flammability	UL 94 V2
	Operating Temperature	-40°F to +221°F (-40°C to +105°C)
	ROHS Compliant	Yes
	Certification/Specification	UL
	UL Recognized (US and Canada)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	100
	Package Quantity (Metric)	100
	Customs Number(Schedule B)	3926909987