Article Number: 411-06047

Description: Heatshrink Moulded Shapes, 1100 series 90 degree with Rib -MIL, 1106-50-L, FPMX, BK, 1/bag

| | | |
|---|---|---|
| Base Data | | |
| | Local Order Number | 411-06047 |
| | Type | 1106-50-L |
| | Color | Black (BK) |
| | Features and benefits | • Used in conjunction with a circular grooved adaptor for strain relief. |
| | Quantity Per | bag |
| | Product Description | Helashrink 1100 series, with rib - MIL style, provides strain relief for harness systems when used in conjunction with a circular grooved adaptor. |
| | Short Description | Heatshrink Moulded Shapes, 1100 series 90 degree with Rib -MIL, 1106-50-L, FPMX, BK, 1/bag |
| Product Dimensions | | |
| | HW ± 20 % b | 1.3mm |
| | HW ± 20% b (imperial) | .05" |
| | H max b (imperial) | .41" |
| | H min a (imperial) | .81" |
| | J min. a (imperial) | .44" |
| | P ±10% b (imperial) | .79" |
| | S nom (imperial) | .23" |
| | T ± 20% b (imperial) | .04" |
| | Variant | For plug |
| | Flexibility | Flexible |
| | H max b | 10.4mm |
| | H min a | 20.8mm |
| | J max. b | 5.6mm |
| | J min. a | 11.2mm |
| | P ±10 % b | 20.3mm |
| | S nom (metric) | 5.8mm |

| | | |
|---|---|---|
| Material and Specifications | | |
| | Material | Fluoroelastomer (FPM) |
| | Material Shortcut | FPMX |
| | Dielectric Strength (Metric) | 9 kV/mm according to ASTM D2671 |
| | Flammability | ASTM D635 |
| | Shrink Temperature | +275 °F (+135 °C) |
| | Operating Temperature | -67°F to +392°F (-55°C to +200°C) |
| | ROHS Compliant | Yes |
| Logistic and Packaging | | |
| | Package Quantity (Imperial) | 1 |
| | Package Quantity (Metric) | 1 |