422-30100

Article Number: 422-30100

Description: Heatshrink Moulded Shapes, Long tail right angle boot, 333F343-9, PO-X, BK, 5/bag

Base Data		
	Local Order Number	422-30100
	Type	333F343-9
	Color	Black (BK)
	Features and benefits	• Connector strain relief for small cable diameters requiring high shrink ratio.
	Quantity Per	bag
	Product Description	Helashrink 313C series is used with a circular grooved adapter to provide strain relief and if adhesive is used, excellent environmental sealing can be achieved. The convoluted design provides the flexibility to accommodate different cable outlet angles.
	Short Description	Heatshrink Moulded Shapes, Long tail right angle boot, 333F343-9, PO-X, BK, 5/bag
Product Dimensions		
	H max b (imperial)	.72"
	H min a (imperial)	1.21"
	J min. a (imperial)	.95"
	P ±10% b (imperial)	5.71"
	Shrink Ratio	3:1
	Variant	For plug
	Flexibility	Flexible
	H max b	18.5mm
	H min a	30.9mm
	J max. b	8.9mm
	J min. a	24.3mm
	P ±10 % b	146.3mm
Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)

Material and Specifications	Material Shortcut	PO-X
	Flammability	ASTM D635
	Shrink Temperature	+212 °F (+100 °C)
	Operating Temperature	-67°F to +248°F (-55°C to +120°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	5
	Package Quantity (Metric)	5Pieces
	Content Unit (BMEcat)	pieces
	Weight (Metric)	0.01kg