PANDUIT P/N	WEIGHT
P18B24M	4.6kg



REAR VIEW



TOP VIEW



FRONT VIEW

NOTES:

1. IDENTIFICATION:

UNIT TYPE:	BASIC
ORIENTATION:	VERTICAL, HALF
OUTLET QTY&TYPE:	(18) C13
BREAKER QTY&TYPE:	(3) 20AMP, DOUBLE-POLE
INPUT VOLTAGE:	100-120/200-240VAC WYE
INPUT CURRENT:	30A (24A DERATED)
INPUT PHASE:	THREE-PHASE WYE
RATED POWER:	8.6kVA
INPUT PLUG:	NEMA L21-30P
INPUT CORD LENGTH:	3m [10']

2. ACCESSORIES:
   POCKET GUIDE
3. RoHS COMPLIANT
4. VISIT PANDUIT'S ON-LINE CATALOG AT WWW.PANDUIT.COM FOR ADDITIONAL PRODUCT INFORMATION CONTAINED IN THE SPECIFICATION SHEET AS WELL AS A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
5. MAXIMUM ALLOWABLE INPUT POWER = 8.6kW
6. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES



SIDE VIEW

PLUG
30 AMP, 120/208V x 3~ WYE
TWIST LOCK
NEMA L21-30P



EIGHTEEN (18)
RECEPTACLES
10 AMP, 250V
STRAIGHT BLADE
IEC 60320 / C13

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX.
THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY

SIGN
DATE
PRINT

TITLE
BASIC SERIES PDU
P18B24M
CUSTOMER DRAWING

ITEM REVISION NAME

DATASHEET FILE NAME:

PANDUIT

UNLESS OTHERWISE SPECIFIED
DIMENSIONAL TOLERANCE ARE: mm [IN]

THIRD ANGLE PROJECTION

Tolerance(mm)	
0<L<200	±0.5
200<L<500	±1.5
500<L<1000	±2.5
1000<L<2000	±4.0

MATERIAL/COLOR: N/A

DRAWING NUMBER: P18B24M_DC

DRAWN BY	DATE	CHK	SCALE		SCALE
JIANG	05/24/2017	SEAN	NONE	SHT 1 OF 1	B