Product Specifications

2160046-4

Fiber Optic Patch Cord, OM4, LC duplex to LC duplex, 1.8 mm LSZH, 4 m, aqua

Body Features

Cable Color	Aqua
Boot Color (End A)	Blue
Boot Color (End B)	Blue
Boot Type (End A)	Bend limiting
Boot Type (End B)	Bend limiting
Connector Color (End A)	Beige
Connector Color (End B)	Beige

Configuration Features

Number of Fibers	2
Number of Connectors (End A)	2
Number of Connectors (End B)	2
Exit Angle to Exit Angle	180° to 180°

Dimensions

Assembly Length	4.00 m | 13.12 ft
Cable Outer Diameter	.071 x .147 in | 1.8 x 3.75 mm

Industry Standards

Flammability Rating	LSZH

Product Availability

Region	North America

Product Type Features

Product Type	Patch Cord (duplex)
System	AMP NETCONNECT | MPOptimate®
Connector Type (End A)	LC/UPC
Connector Type (End B)	LC/UPC
Fiber Type	OM4
Fiber Diameter	50/125 µm
Connector Style (End A)	Duplex
Connector Style (End B)	Duplex
Ferrule Material	Zirconia
Fiber Cable Buffering	Tight buffer
Fiber Cable Type	Duplex, dualzip

©2017 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope.
All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: May 19, 2017

Product Specifications

2160046-4

Optical Mode	Multimode
Polarity	Pair Flipped

Signal Characteristics

Insertion Loss, maximum (End A)	0.15 dB
Insertion Loss, maximum (End B)	0.15 dB

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant

* Footnotes

Assembly Length	Assembly length includes the breakout lengths

©2017 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope.
All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: May 19, 2017