Product Specifications

COMMSCOPE

4-1206114-4

Fiber Optic Termination Panel, 1U, 19 in, 24 ST/PC, multimode, black

Body Features

Chassis Color	Black
Finish	Powder coated

Configuration Features

Number of Ports	24
Front Connector Type	ST/UPC
Configuration	Adapters only
Number of Fibers	24
Port Style	Simplex

Dimensions

Height	44.450 mm | 1.750 in
Width	482.600 mm | 19.000 in

Other

Comment	With Sliding Tray

Packaging Features

Includes	Installation Instruction | Mounting hardware
Packaging Method	Box/Carton
Packaging Quantity	1

Product Availability

Region	EMEA

Product Type Features

Product Type	Fiber Termination Panel
System	AMP NETCONNECT
Rack Units	1.0
Optical Mode	Multimode

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant

©2017 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope.
All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: May 19, 2017