SIEMENS

Data sheet US2:P4260L1225CU

1PH LC 42S 60C ML 200A CU INDOOR

Configuration of the busbars	225A
Mounting type	Combination
Phase number	1
Suitability for operation	Residential

Electricity

Ampacity	225 A
Voltage between phase and Ground (GND) rated value	120 V
Voltage between phase and phase rated value	240 V

Switching capacity

Switching capacity current acc. to EN 60898 rated value	22000 A

Model

product brandname	Siemens
Product sub brand name	Load Centers
Product type designation	1

Mechanical Design

Number of width units for installation width	42

Subject to change without notice
© Copyright Siemens

Width [in]	3806.5 in

last modified: 06/29/2017

Subject to change without notice
© Copyright Siemens