
LC CONNECTOR PRODUCTS

Siemon LC products offer all the benefits of SC and ST connectors in a Small Form Factor (SFF), high-density design. LC adapter products are compatible with our popular MAX®, CT®, FOB and MX-SM® work area products and our telecommunications room products, providing a wide variety of installation options. All fiber adapters are "universal" and support either multimode or singlemode fiber connections. LC connectors take just 2 minutes to terminate, using the Siemon LightSpeed® Termination Kit with LC upgrade option. Both multimode solutions and singlemode products are available.



WORK AREA SOLUTIONS



Simplex & Duplex LC Fie

Flat MAX LC Module in MX-SM Box (MX-SM2-(XX) shown)



MAX® LC Modules in MAX Faceplate [MX-FP-S-04-(XX) shown]




CT® Flat & Angled LC Couplers in CT Faceplate [CT8-FP-(XX) shown]



MAX & CT LC Modules in Multi-user Telecommunications Outlet (MuTOA) [CT-MMO-(XX) shown]



FOB LC Bezels in Fiber Outlet Box [FOB2-(XX) shown]



LightSystem[©]



LC — Simplex



LC — LC Duplex

ld-Installable Connectors


TELECOMMUNICATION ROOM SOLUTIONS



LC Quick-Pack™ Adapter Plate in RIC3-48

Plate in SWIC3

The Rack Mount Interconnect Center provides high-density fiber management and distribution for up to 288 fibers in just 4 RMS. Available in 24- to 96-port, 36- to 144-port, 48- to 192-port and 72- to 288-port.



LC Quick-Pack Adapter

The Wall Mount Interconnect Center is designed to manage and connect up to 48 fibers. Available with or without integrated jumper guard and with various lock or latch options. A Mini-SWIC3 (SWIC3-M) is also available.

LC Jumpers



LC — SC Duplex



LC - ST Duplex



LC Quick-Pack Adapter Plate in FCP3-DWR

The Fiber Connect Panel rack mount enclosures economically connect, protect and manage up to 36 fibers within one Rack Mount Space (RMS).

LC Work Area Solutions:

LC Field-Installable Connectors Multimode

FC1-LC-MM-B80	LC Simplex con	nector, multimode,
	buffered fiber, l	beige boot
		1. 1

FC2-LC-MM-J80LC Duplex connector, multimode, jacketed fiber, beige boot

Singlemode

FC1-LC-SM-B02	LC Simplex conn	nector, singlemode,
	buffered fiber, w	hite boot

	,	
FC1-LC-SM-J02	LC Simplex connector jacketed fiber, white l	r, singlemode, poot

Note: Siemon LC jacketed fiber connectors require the use of 1.6mm jacketed fiber cables.

 Add "-B" to the end of part number for bulk pack (simplex: 100/box; duplex: 50/box)

LC MAX® Module

MX-F1-LC(X)-(XX).......Flat module with 1 duplex LC adapter (2 fibers)

Use (X) to specify LC adapter color: blank = beige, U = blue Use (XX) to specify color: 01 = black, 02 = white, 04 = gray, 20 = ivory, 25 = bright white, 80 = light ivory

Modules include dust caps, one color-matching, one red, and one blue icon per port

LC CT® Couplers

CT-LC(X)-(XX)	Flat coupler with 1 duplex LC adapter
, , , ,	(2 fibers)
CT-LC(X)-LC(X)-(XX)	Flat coupler with 2 duplex LC adapters
, , , , , ,	(4 fibers)
CT A LCDVI DVVI	A

CT-A-LC(X)-(XX)Angled coupler with 1 duplex LC adapter (2 fibers)

CT-A-LC(X)-LC(X)-(XX) ...Angled coupler with 2 duplex LC adapters (4 fibers)

Use (X) to specify LC adapter color: blank = beige, U = blue Use (XX) to specify color: 01 = black, 02 = white, 04 = gray, 20 = ivory, 80 = light ivory

Couplers include one color-matching icon (clear for black), plus one red and one blue icon

LC Fiber Outlet Box (FOB) Bezels

FOB-BZL-LC(X)1-011 Duplex LC adapter (2 fibers)	
FOB-BZL-LC(X)-012 Duplex LC adapters (4 fibers)	
Use (X) to specify LC adapter color: blank = beige, U = bl	ue

Because we continuously improve our products, Siemon reserves the right to change specifications and availability without prior notice.

CT®, XGLO™, LightSpeed®, LightSystem®, MAX®, Quick-Pack™and SM® are trademarks of Siemon

The Americas

Watertown, CT USA Phone (1) 860 945 4200

Europe/Middle East/Africa

Surrey, England Phone (44) 0 1932 571771

LC Modular Patching Solutions:

LC Quick-Pack™ Adapter Plates

RIC-F-LC(X)12-016 duplex LC adapters (12 fibers)	
RIC-F-LC(X)16-014 quad LC adapters (16 fibers)	
RIC-F-LC(X)24-016 quad LC adapters (24 fibers)	
Use (X) to specify LC adapter color: $blank = beige$, $U = blue$	

LightSystem® LC Jumpers

Duplex
FJ2-LCLC(X)MM-(XX)LC to LC multimode, orange jumper
FJ2-LCULCU-(XX)LC to LC singlemode, yellow jumper
FJ2-LCSA(X)MM-(XX)LC to ST multimode, orange jumper
FJ2-LCUSAU-(XX)LC to ST singlemode, yellow jumper
FJ2-LCSC(X)MM-(XX)LC to SC multimode, orange jumper
FJ2-LCUSCU-(XX)LC to SC singlemode, yellow jumper

Simplex
FP1B-LC-(X)MM-01......LC pigtail multimode, orange jacket, 900 micron, buffered, 1 m (3.3 ft.)

FP1B-LCU-01LC pigtail singlemode pigtail, yellow jacket, 900 micron, buffered, 1m (3.3 ft.)

Use (X) to specify multimode fiber type: $"-" = 62.5/125\mu m$, orange jacket, $5 = 50/125\mu m$ (orange jacket)

Use (XX) to specify cable length: 01=1m (3.3 ft.), 02=2m (6.6 ft.), 03=3m (9.8 ft.), 05=5m (16.4 ft.)

Notes: Multimode performance: 0.15 dB typical insertion loss; 30 dB typical return loss; Singlemode performance: 0.25 dB typical insertion loss; 57 dB return loss

Tools:

Siemon LightSpeed® Termination Kit

FTERM-L2	LightSpeed Termination Kit*
	Consumables Kit for FTERM-L2**

*All consumables including primer, adhesive, wipes, alcohol pads and polishing films are contained in the consumables kit and must be ordered separately. Contents of the FTERM Termination Kit are also available individually.

**This product contains material with a time and temperature sensitive shelf life.

LC Fiber Termination Upgrade Kit

FTERM-LC.....LC Fiber Termination Kit (used in conjunction with FTERM-L2)

Note: Contents of FTERM-LC are also available individually.

For related product information request Spec Sheet(s):

CT Faceplates (PROD-SS-CTF)
MAX Modular Faceplates (PROD-SS-MXF)
Fiber Outlet Box (PROD-SS-FOB)
Multi-user Telecommunications Outlet (MuTOA) (PROD-SS-MMO)
Wall Mount Interconnect Center (SWIC2) (PROD-SS-WI2)
MX-SM Series Surface Mount Box (PROD-SS-RIC)
Rack Mount Interconnect Center (PROD-SS-RIC)
LightSystem Jumper & Pigtails (PROD-SS-FJI)
XGLO Jumpers and Pigtails (PROD-SS-LOF)
LightSpeed Fiber Termination Kit (PROD-SS-FTK)

Asia/Pacific

Shanghai, P.R. China Phone (86) 21 6390 6778



