

STM-8

The STM-8 is an economical and versatile hand-held tester designed for testing UTP and screened (ScTP) cable for opens, shorts, reversals, miswires, split pairs and cable length. Its rugged state-of-the-art construction, easy-to-read LCD display, and multiple remotes allow one person to quickly test and identify up to four different cable runs from one location.

A low battery status indication is provided, as well as automatic shut-off to extend battery life

Test cable runs up to 900m (2950 ft.)



Indications for 6- and 8-position jacks

The presence of line voltage is indicated on the display to help prevent accidental damage to the unit

The UTP modular cords are equipped with patented "universal" plugs, that fit any standard 6- or 8- position jack

Additional remotes can be purchased separately



Tests all wiring configurations — T568A, T568B, USOC, 10BASE-T, Token Ring, and TP-PMD

In the FIND mode, the STM-8 will detect and identify which wiring scheme is present in the cable being tested

In the LENGTH mode, the STM-8 will determine the distance measurements on any given cable up to 900m (2950 ft.). This feature may be used with all four identifiable remotes


CE
PATENTED

TOOLS AND TESTERS

STM-8



STM-8.....UTP (unshielded, twisted-pair) cable tester. Includes carrying case, remote "A", two universal modular plug cords, wiring guide, 9V alkaline battery, instructions, and warranty card



STM8-R(X)Additional identifiable UTP passive remotes

Use (X) to specify remote:
A = remote A, 3 = kit of remotes B, C, and D

STM-8-S



STM-8-S.....Screened twisted-pair cable tester. Includes carrying case, active remote, two screened universal plug-ended modular cords, wiring guide, 9V alkaline battery, instructions, and warranty card



STM8-RA-S.....Active remote for UTP/ScTP with two screened modular cords, instructions, 3V lithium battery, and warranty card

S110° Test Adapters:

- TAP-110-T4Category 5, 4-pair S110 test adapter, T568A
- TAP-110-A4Category 5, 4-pair S110 test adapter, T568B

S66™ Test Adapters:

- TESTAR-8T-C5.....Category 5 compatible, 4-pair, 8-position, TESTAR®, T568A wiring
- TESTAR-8A-C5.....Category 5 compatible, 4-pair, 8-position, TESTAR, T568B wiring

Because we are continuously improving our products, The Siemon Company reserves the right to change specifications and availability without prior notice. S110°, S66™ and TESTAR® are trademarks of The Siemon Company

The Americas
Watertown, CT USA
Phone (1) 860 945 4200

Europe/Middle East/Africa
Surrey, England
Phone (44) 0 1483 480040

Asia/Pacific
Shanghai, P.R. China
Phone (86) 21 6390 6778