REAR COMPARTMENT LOCKS

Ford	Galaxie 500	1965-78	see LTD				
Ford	Granada	1974-80	Coded lock	B-42-107 TL1553	Uncoded lock	TL1553U	Use tumbler series P-42-131/135
Ford	Granada sedan	1981-82	Coded lock	B-42-135	Use tumbler series P-42-131/135		
Ford	Granada station wagon	1981-82	Coded lock	B-42-108 TL1554	Uncoded lock	TL1554U	Use tumbler series P-42-131/135
Ford	LTD sedan	1965- 2/76	Coded lock	B-42-105 TL1552	Uncoded lock	TL1552U	Use tumbler series P-42-131/135
Ford	LTD sedan	2/76-82	Coded lock	B-42-107 TL1553	Uncoded lock	TL1553U	Use tumbler series P-42-131/135
Ford	LTD sedan	1983-86	Coded lock	B-42-135	Use tumbler series P-42-131/135		
Ford	LTD wagon	1965-80	see Country Sedan / Country Squire				
Ford	LTD wagon	1981-86	Coded lock	B-42-108 TL1554	Uncoded lock	TL1554U	Use tumbler series P-42-131/135
Ford	LTD II sedan	1977-79	Coded lock	B-42-107 TL1553	Uncoded lock	TL1553U	Use tumbler series P-42-131/135
Ford	LTD II wagon	1977-79	Coded lock	B-42-102	Use tumbler series P-42-131/135		
Ford	Maverick	1970-78	Coded lock	B-42-105 TL1552	Uncoded lock	TL1552U	Use tumbler series P-42-131/135
Ford	Mustang	1964-66	No longer available – try classic Ford parts specialists. Use tumbler series P-42-181/185				
Ford	Mustang	1967-73	Coded lock	B-42-105 TL1552	Uncoded lock	TL1552U	Use tumbler series P-42-131/135
Ford	Mustang II	1974-78	Coded lock	B-42-135	Use tumbler series P-42-131/135		
Ford	Mustang	1979-86	Coded lock	B-42-107 TL1553	Uncoded lock	TL1553U	Use tumbler series P-42-131/135
Ford	Mustang	1987-93	Uncoded lock	B-42-128	Use tumbler series P-42-131/135		
Ford	Mustang 10-cut locks	1994-95	Uncoded service pack	B-42-267	Use face cap P-42-202 (black) Use tumbler series P-42-141/145		
Ford	Mustang 8-cut locks	1995-96	Replacement locks available from Ford dealers only. Use face cap P-42-265 (black) Use tumbler series P-42-061/065				
Ford	Mustang 8-cut locks	1997-04	Uncoded service pack	TL6179U	Coded lock	TL6179	Use face cap P-42-265 (black) or P-42-266 (chrome) Use tumbler series P-42-061/065
Ford	Mustang	2005-07	Replacement locks available from Strattec Use tumbler series P-42-061/065				
Ford	Pinto except station wagon	1971-80	Coded lock	B-42-105 TL1552	Uncoded lock	TL1552U	Use tumbler series P-42-131/135
Ford	Pinto station wagon	1971-80	Uncoded lock	D-42-201	Use pawl P-42-389 Use tumbler series P-42-131/135		
Ford	Probe	1989-92	Complete lock	B-20-143	Use face cap P-20-210 Use tumbler series P-20-111/164		
Ford	Probe	1993-97	Complete lock	B-20-127	Use face cap P-20-210 Use tumbler series P-33-101/105		
Ford	Taurus sedan	1986-91	Coded lock	B-42-129 TL1573	Use tumbler series P-42-131/135		
Ford	Taurus sedan	1992-95	Coded lock chrome	B-42-121 TL5077	Use tumbler series P-42-131/135		
			Coded lock black (SHO model)	B-42-123 TL5078	Use tumbler series P-42-131/135		
Ford	Taurus station wagon	1986-95	Coded lock	B-42-147	NOTE: The original shaft must be reused. Use tumbler series P-42-131/135		
Ford	Taurus	1996-08	Replacement locks available from Strattec Use face cap P-42-266 Use tumbler series P-42-061/065				
Ford	Tempo	1984-87	Coded lock chrome	B-42-135	Coded lock black	B-42-126	Use tumbler series P-42-131/135
Ford	Tempo 2-door	1988-94	Coded lock chrome	B-42-135	Coded lock black	B-42-126	Use tumbler series P-42-131/135
			Coded lock – black face cap with chrome dust cover			B-42-127	
Ford	Tempo 4-door	1988-94	Coded lock chrome	B-42-129 TL1573	Coded lock black cap / chrome dust cover	B-42-130	Use tumbler series P-42-131/135
Ford	Thunderbird	1955-71	Try classic Ford parts specialists. For 1955-64 models use tumbler series P-42-181/185 (single sided keys) For 1965-71 models use tumbler series P-42-131/135 (double sided keys)				
Ford	Thunderbird	1972-76	Coded lock	B-42-105 TL1552	Uncoded lock	TL1552U	Use tumbler series P-42-131/135
Ford	Thunderbird	1977-88	Coded lock chrome	B-42-135	Coded lock black	B-42-126	Use tumbler series P-42-131/135
			Coded lock – black face cap with chrome dust cover			B-42-127	
Ford	Thunderbird pin tumbler lock	1989-96	Coded lock chrome no factory alarm	B-42-129 TL1573	Uncoded lock chrome no factory alarm	B-42-117 TL1573U	Use tumbler series P-42-131/135
			Coded lock black no factory alarm	B-42-130 TL1572	Uncoded lock black no factory alarm	TL1572U	Use tumbler series P-42-131/135
			Coded lock chrome with factory alarm	B-42-118	Use tumbler series P-42-131/135		
			Coded lock black with factory alarm	B-42-142	Use tumbler series P-42-131/135		

Lexus	LS400	1990-92	Complete lock	B-30-181	Use tumbler series P-30-110/119		
Lexus	LS400	1993-94	Complete lock	B-30-184	Use tumbler series P-30-110/119		
Lexus	LS400	1995-97	Complete lock	B-30-186	Use tumbler series P-30-110/119		
Lexus	LS400	1998-00	Complete lock	B-30-190	Use tumbler series P-30-121/123		
Lexus	LS430	2001-06	Replacement locks available from Lexus dealers only. Use tumbler series P-30-121/123				
Lexus	LS460	2007	Replacement locks available from Lexus dealers only. Use tumbler series P-30-121/123				
Lexus	LX450	1996-97	Complete lock	B-30-185	Use tumbler series P-30-110/119		
Lexus	LX470	1998-00	Complete lock	B-30-191	Use tumbler series P-30-110/119		
Lexus	LX470	2001-06	Replacement locks available from Lexus dealers only. Use tumbler series P-30-121/123				
Lexus	RX300	1998-03	Complete lock	B-30-192	Use tumbler series P-30-121/123		
Lexus	RX330, RX350	2004-07	Replacement locks available from Lexus dealers only. Use tumbler series P-30-121/123				
Lexus	SC300, SC400	1992-00	Complete lock	B-30-187	Use tumbler series P-30-110/119		
Lexus	SC430	2002-07	Replacement locks available from Lexus dealers only. Use tumbler series P-30-121/123				
Lincoln	All	1952-65	Replacement locks no longer available – try classic Ford / Lincoln / Mercury parts specialists Use tumbler series P-42-181/185 to service the locks originally installed on the car when it was new.				
Lincoln	All	1966-76	Coded lock	B-42-105 TL1552	Uncoded lock	TL1552U	NOTE: There may be some variation in applications 1966-80, check the picture section to be sure. Use tumbler series P-42-131/135
Lincoln	All	1977-80	Coded lock	B-42-107 TL1553	Uncoded lock	TL1553U	
Lincoln	Aviator	2003-05	Remote release only, no lock cylinder.				
Lincoln	Blackwood	2002-03	Uncoded service pack	DL5885U	Coded lock (available only as a keyed alike pair)	DL5885	Use face cap P-42-267 Use tumbler series P-42-061/065
Lincoln	Continental	1982-87	Coded lock	B-42-135	Use tumbler series P-42-131/135		
Lincoln	Continental	1988-94	Coded lock chrome no factory alarm	B-42-129 TL1573	Uncoded lock chrome no factory alarm	B-42-117 TL1573U	Use tumbler series P-42-131/135
			Coded lock black no factory alarm	B-42-130 TL1572	Uncoded lock black no factory alarm	TL1572U	Use tumbler series P-42-131/135
			Coded lock chrome with factory alarm	B-42-118	Use tumbler series P-42-131/135		
			Coded lock black with factory alarm	B-42-142	Use tumbler series P-42-131/135		
Lincoln	Continental pin tumbler lock	1995-96	Uncoded lock no factory alarm	B-42-119	Uncoded lock with factory alarm	B-42-120	Use tumbler series P-42-131/135
Lincoln	Continental 8-cut locks	1996-02	Replacement locks available from Strattec Use tumbler series P-42-061/065				
Lincoln	Mark LT	2006-08	Uncoded service pack	DL5885U	Coded lock (available only as a keyed alike pair)	DL5885	Use face cap P-42-267 Use tumbler series P-42-061/065
Lincoln	Mark III Mark IV	1969 to 2/76	Coded lock	B-42-105 TL1552	Uncoded lock	TL1552U	Use tumbler series P-42-131/135
Lincoln	Mark V Mark VI	2/76 to 1980	Coded lock	B-42-107 TL1553	Uncoded lock	TL1553U	Use tumbler series P-42-131/135
Lincoln	Mark VI	1981-84	Coded lock	B-42-135	Use tumbler series P-42-131/135		
Lincoln	Mark VII	1984-92	Coded lock no factory alarm	B-42-135	Uncoded lock with factory alarm	B-42-136	Use tumbler series P-42-131/135
Lincoln	Mark VIII pin tumbler lock	1993-96	Uncoded lock	B-42-139	Use tumbler series P-42-131/135		
Lincoln	Mark VIII 8-cut locks	1996-98	Replacement locks available from Strattec Use tumbler series P-42-061/065				
Lincoln	MKX	2007-08	Replacement locks available from Ford-Lincoln-Mercury dealers only.				
Lincoln	MKZ	2007-08	Replacement locks available from Ford-Lincoln-Mercury dealers only.				
Lincoln	Navigator	1998-06	Replacement locks available from Strattec Use face cap P-42-266 Use tumbler series P-42-061/065				
Lincoln	Navigator	2007-08	Remote release only, no lock cylinder				
Lincoln	Town Car	1980-89	Coded lock no factory alarm	B-42-135	Uncoded lock with factory alarm	B-42-136	Use tumbler series P-42-131/135
Lincoln	Town Car pin tumbler lock	1990-96	Coded lock chrome no factory alarm	B-42-129 TL1573	Uncoded lock chrome no factory alarm	B-42-117 TL1573U	Use tumbler series P-42-131/135
			Coded lock chrome with factory alarm	B-42-118	Use tumbler series P-42-131/135		
Lincoln	Town Car 8-cut locks	1996-07	Replacement locks available from Ford-Lincoln-Mercury dealers only. Use face cap P-42-266 Use tumbler series P-42-061/065				
Lincoln	Versailles	1978-80	Coded lock	B-42-107 TL1553	Uncoded lock	TL1553U	Use tumbler series P-42-131/135
Lincoln	Zephyr	2006-07	Replacement locks available from Ford-Lincoln-Mercury dealers only.				
Lotus	All	All	see the Exotic Brands section				

REAR COMPARTMENT LOCKS

Mercedes-Benz	W201	1984-93	Complete lock	B-21-130	Use tumbler series P-21-121/135		
Mercedes-Benz	W202, W210	1994-99	Complete lock	B-21-131	Use tumbler series P-21-171/185		
Mercedes-Benz	M-Class	1998-08	Replacement locks available from Mercedes-Benz dealers only. Use tumbler series P-21-171/185				
Mercedes-Benz	Sprinter	2003-06	Uncoded plug	D-21-102	Use tumbler series P-21-191/194		
Mercedes-Benz	Sprinter	2007-08	Replacement locks available from Mercedes-Benz dealers only.				
Mercury	All	1952-64	Replacement locks available from Ford / Lincoln-Mercury dealers or classic Ford parts specialists only. Use tumbler series P-42-181/185				
Mercury	Bobcat except station wagon	1971-80	Coded lock	B-42-105 TL1552	Uncoded lock	TL1552U	Use tumbler series P-42-131/135
Mercury	Bobcat station wagon	1971-80	Uncoded lock	D-42-201	Use pawl P-42-389 Use tumbler series P-42-131/135		
Mercury	Capri	1970-75	Replacement locks available from Ford / Lincoln-Mercury dealers or classic Ford parts specialists only. Service parts and tumblers not available				
Mercury	Capri	1976-78	Complete lock	B-18-105	Use tumbler series P-18-111/114		
Mercury	Capri	1979-86	Coded lock	B-42-107 TL1553	Uncoded lock	TL1553U	Use tumbler series P-42-131/135
Mercury	Capri	1990-94	Complete lock	B-20-104	Use face cap P-20-211 (chrome) or P-20-212 (black) Use tumbler series P-20-111/164		
Mercury	Colony Park station wagon	1965-91	Coded lock – cylinder separate from the door handle)	B-42-102	Use tumbler series P-42-131/135		
			For cars with lock cylinder in the door handle, replacement locks available from Ford dealers only.				
Mercury	Comet	1960-65	Replacement locks available from Ford / Lincoln-Mercury dealers or classic Ford parts specialists only. Use tumbler series P-42-181/185				
Mercury	Comet	1966-69	Coded lock	B-42-103	Use tumbler series P-42-131/135		
Mercury	Comet	1971-78	Coded lock	B-42-105 TL1552	Uncoded lock	TL1552U	Use tumbler series P-42-131/135
Mercury	Cougar	1967-76	Coded lock	B-42-105 TL1552	Uncoded lock	TL1552U	Use tumbler series P-42-131/135
Mercury	Cougar except station wagon	1977-82	Coded lock chrome	B-42-135	Use tumbler series P-42-131/135		
Mercury	Cougar station wagon	1981-82	Coded lock	B-42-108 TL1554	Uncoded lock	TL1554U	Use tumbler series P-42-131/135
Mercury	Cougar	1983-88	Coded lock chrome	B-42-135	Coded lock black	B-42-126	Use tumbler series P-42-131/135
			Coded lock – black face cap with chrome dust cover			B-42-127	
Mercury	Cougar pin tumbler lock	1989-96	Coded lock chrome no factory alarm	B-42-129 TL1573	Uncoded lock chrome no factory alarm	B-42-117 TL1573U	Use tumbler series P-42-131/135
			Coded lock black no factory alarm	B-42-130 TL1572	Uncoded lock black no factory alarm	TL1572U	Use tumbler series P-42-131/135
			Coded lock chrome with factory alarm	B-42-118	Use tumbler series P-42-131/135		
			Coded lock black with factory alarm	B-42-142	Use tumbler series P-42-131/135		
Mercury	Cougar 8-cut locks	1996-98	Replacement locks available from Strattec Use face cap P-42-266 Use tumbler series P-42-061/065				
Mercury	Cougar	1999-02	Uncoded service pack	B-42-270	Use face cap P-42-280 Use tumbler series P-42-141/145		
Mercury	Grand Marquis	1983-87	Coded lock	B-42-107 TL1553	Uncoded lock	TL1553U	Use tumbler series P-42-131/135
Mercury	Grand Marquis	1988-91	Coded lock	B-42-135	Use tumbler series P-42-131/135		
Mercury	Grand Marquis	1992-94	Coded lock except police / taxi	B-42-121	Use tumbler series P-42-131/135		
			Uncoded service pack police / taxi	B-42-112	Use face cap P-42-201 Use tumbler series P-42-141/145		
Mercury	Grand Marquis pin tumbler or 10-cut locks	1995-96	Uncoded lock except police / taxi	B-42-113	Use tumbler series P-42-131/135		
			Uncoded service pack police / taxi	B-42-114	Use face cap P-42-201 Use tumbler series P-42-141/145		
Mercury	Grand Marquis 8-cut locks	1996-07	Uncoded service pack exc police, taxi, export	TL6186U	Coded lock	TL6186	Use face cap P-42-266 Use tumbler series P-42-061/065
			Uncoded service pack police, taxi, export	TL6183U	Coded lock	TL6183	Use face cap P-42-266 Use tumbler series P-42-061/065
Mercury	LN7, Lynx	1981-87	Coded lock	B-42-105 TL1552	Uncoded lock	TL1552U	Use tumbler series P-42-131/135
Mercury	Lynx station wagon	1981-87	Coded lock	B-42-108 TL1554	Uncoded lock	TL1554U	Use tumbler series P-42-131/135
Mercury	Marauder	2003-04	see Grand Marquis				
Mercury	Mariner	2005-07	Replacement locks available from Ford / Lincoln-Mercury dealers only Use tumbler series P-42-151/155				
Mercury	Marquis	1970-2/76	Coded lock	B-42-105 TL1552	Uncoded lock	TL1552U	Use tumbler series P-42-131/135
Mercury	Marquis	2/76-1982	Coded lock	B-42-107 TL1553	Uncoded lock	TL1553U	Use tumbler series P-42-131/135

The ASP Part Numbering System

Working with the ASP part numbers is easier if you have a basic understanding of the part numbering system, explained here:

The first letter or letters of the part number identify what type of product the part number is:

A	Keying kits and parts assortments
B	Luggage compartment locks
C	Ignition locks
D	Door locks (including complete locks that include the door handle)
DH	Door handles (except complete locks that include the door handle)
DP	Door locks (keyed alike pair)
E	Engine compartment locks
F	Fasteners (including lock retaining clips, shear-head bolts, door panel fasteners, etc.)
G	Glove compartment and stowage locks
KB	Key blanks
P	Lock service parts (including tumblers, face caps, and other parts)
RK	Remote head key blanks
S	Lock sets
T	Fuel tank locks
W	Ignition switches (wiring assembly only without lock cylinder)

The second two digits of the part number tell you the PRIMARY brand of vehicle that the item is used on:

00	Various cars
11	Alfa Romeo
12	Audi
13	BMW
14	British Cars (Austin, Jaguar, Land Rover, MG, Range Rover, Triumph)
15	British Chrysler (Plymouth Cricket, Sunbeam, Hillman)
16	Nissan / Datsun / Infiniti
17	Fiat
18	European Ford (Capri, Fiesta, Merkur)
19	Honda / Acura
20	Mazda
21	Mercedes-Benz
22	Mitsubishi
23	GM Europe (Cadillac Catera, Pontiac Lemans, Opel)
24	Isuzu (including General Motors brands)
25	Peugeot
26	Porsche
27	Renault
28	Saab
29	Subaru
30	Toyota / Lexus / Scion / Hino truck
31	Volkswagen
32	Volvo
33	Suzuki
34	Lada
35	Lancia
36	Hyundai
37	Daihatsu
38	Citroen
39	Yugo
40	Kia
41	General Motors USA (Buick, Cadillac, Chevrolet, GMC, Oldsmobile, Pontiac)
42	Ford / Lincoln / Mercury (USA)
43	American Motors (including some Heavy Trucks and Jeep)
44	Chrysler / Dodge / Jeep / Plymouth
45	Skoda
49	Saturn
50	Daewoo (including Chevrolet Aveo, Saturn Vue, other General Motors brands)
55	Renault truck (including some Mack trucks)
56	Freightliner truck
57	Kenworth truck
93	Harley Davidson Motorcycle
94	Honda Motorcycle
98	Yamaha Motorcycle

For example, if you have part number C-30-107, by understanding the part numbering system you will know that the part is an ignition lock (first letter C), which fits a Toyota (second two digits 30).

There are exceptions to this system created by the same part being used on more than one brand of car. Also some parts are used in more than one place on the car – for example, B-14-210 is numbered as a luggage compartment lock, but also is used as an ignition lock or door lock on some cars.

ASP PART NUMBERING SYSTEM

The same part being used on more than one brand of car is explained by lock families, as follows:

Audi - also found on some Porsche and Volkswagen

Ford USA – also found on some Mazda and Nissan

Honda / Acura - also found on some Isuzu

Mazda – also found on some Chrysler imports, Ford imports, General Motors imports, GEO, Mitsubishi, Suzuki

Nissan - also found on some Subaru and Isuzu truck

Toyota – also found on some Chrysler imports, Daihatsu, General Motors imports, GEO, Hyundai, Isuzu, Kia, Mazda, Mitsubishi, Suzuki.

Volkswagen - also found on some Audi and Porsche (tumblers also used on BMW)

You will also find some parts that are used among the brands of the following groups of cars:

British cars - Aston Martin, Austin, English Ford, Jaguar, Jensen, Land Rover, MG, Morgan, Range Rover, Rover car, Sterling car, Triumph, TVR, Volvo.

French cars - Peugeot, Renault, Citroen

German cars - Audi, BMW, Daewoo, General Motors (Cadillac Catera, Chevrolet Aveo, Pontiac Lemans, others), Mini, Porsche, Mercedes-Benz, Volkswagen

Italian cars - Alfa Romeo, Bertone, Ferrari, Fiat, Iveco, Lada, Lamborghini, Lancia, Maserati, Pininfarina, Yugo

Lockcraft Part Numbers

The first two letters of the part number identify what type of product the part number is:

DL	Door lock
LC	Ignition lock
LS	Lock set
RP	Lock service parts (including tumblers, face caps, and other parts)
SK	Keying kits and parts assortments
TL	Luggage compartment locks

Lockcraft part numbers that end in “U” are uncoded locks.

There have been many changes to the Lockcraft part numbers over the past years, explained as follows:

Most old Lockcraft part numbers had no letter prefix. For example, old part number 1426 was changed to LC1426 to identify the type of product.

Some old Lockcraft part numbers had a letter prefix “A”, which was changed to “RP”. For example, part number A6001 was changed to RP6001. This could be confusing if you have an old Lockcraft or All Lock keying kit or parts assortment which identified the parts inside by the letter prefix “A”. When reordering simply change the “A” to “RP”.
Some old Lockcraft part numbers had a digit “3” at the end of the part number, which designated poly bag packaging. For example, part number LC14263 designated the LC1426 ignition lock in a poly bag. The currently used part numbers now eliminate the “3” at the end and using the example LC14263 is now simply LC1426.

Some old Lockcraft part numbers had a digit “8” at the end of the part number, which designated that it was an uncoded lock. For example, part number LC14268 designated the LC1426 ignition lock in uncoded form. The currently used part numbers now use “U” at the end of the part number instead of the “8”. Using the example LC14268 is now LC1426U.

Part Number Listings and Popularity Ratings

Pages 214-233 contain a complete listing of ASP part numbers, with the 2008 popularity rating for each part number.
The popularity ratings are explained as follows:

A = Most popular items (lock cylinders and replacement parts)

B = Second most popular group of lock cylinders

Y = Replacement parts (keying kit refill tumblers, face caps, etc.), popularity equivalent to B-rated lock cylinders

C = Third most popular group of lock cylinders

Z = Replacement parts (keying kit refill tumblers, face caps, etc.), popularity equivalent to C-rated lock cylinders

H = Items not recommended for stock by distributors, these parts are normal stock items for the ASP warehouse and available for drop shipments (HI-SPEED delivery). Orders must be placed through your distributor, and are subject to stock on hand at ASP. Some distributors may have selected H-rated items in stock.

S = Special order items only, may not be in stock at ASP. These items may be subject to minimum order quantities if needed. Some distributors may have selected S-rated items in stock.

DWO = Discontinued when out. Some items may still have limited stock at ASP or at some distributors, but will not be restocked when existing supplies are sold out.

ASP products are sold through the network of locksmith supply distributors located throughout the USA and Canada.

With over 4,000 different part numbers in our range, it is impossible and impractical for distributors to keep every part number in stock. Thus we have assigned each of our part numbers a popularity rating to assist distributors in keeping stock. We have implemented new distributor stocking programs based on these popularity ratings. Please check www.carlocks.com for the most current information about our distributor stocking guidelines. ASP is working closely with our distributors to provide you the fastest delivery possible at the lowest possible cost.

Distributors who make a commitment to keep stock according to our recommendations are listed on www.carlocks.com
This list is subject to change at any time. Distributors who do not keep the stocking commitment will be removed from the list.

Explanation of other notes on the part number listing

a. Some items have (now use …) to the right of the part number, with a rating of DWO.
For example: A-13-105 (now use A-31-110) – this means that A-13-105 has been superseded by A-31-110.

b. Some items have (substitute …) to the right of the part number, with a rating of DWO.
For example: B-19-154 (substitute B-19-155) - this means that you can substitute B-19-155 for B-19-154, but there is some difference between the two parts. A complete listing of these part numbers with a brief explanation of the difference between each superseded part and the replacement part is provided on pages 234-237.

c. Some items have (see …) to the right of the part number, with no popularity rating.
For example: B-16-105 (see B-16-205), with no popularity rating. Then go to B-16-205 and you will see it listed as B-16-205 (B-16-105) with the popularity rating of B. This is a result of our consolidating some similar interchangeable part numbers. In this example, whether you order B-16-105 or B-16-205, you will get the same part at the same price. A complete listing of these part numbers is provided on pages 238-239.