

CU-8R – Area of Rescue Command Unit

Description

This fully Integrated Command Unit accommodates up to 8 ADA-compliant Area of Rescue Stations. The unit's Strobe/Sounder indicates an incoming call, and LED's indicate the calling location.

Features

- Accommodates up to 8 ADA compliant Area of Rescue Stations
- Stations are powered by Command Unit
- LEDs on Command Unit indicate calling Station and line status
- On-site calling requires no outside phone lines
- Off-site calling requires only one phone line for up to 8 Stations: line seizure eliminates need for dedicated phone line
- Blinking LEDs indicate Stations that are waiting to be answered. When first call is completed, 2nd call is automatically placed, phone rings and strobe/siren is activated
- Siren is activated when Emergency call is first detected, shuts off when call has been answered
- Strobe is activated when Emergency call is first detected and remains active for duration of call
- Included UPS (mounted outside cabinet) provides 4 hour power back-up in case of power failure
- Includes built-in phone



CU-8R

Specifications

Sound:	Sounder ranges from 90 to 100 dBA, has 8 sound options
Construction:	16 gauge #4 brushed stainless steel cabinet, acrylic windows
Dimensions:	12.62(321) W x 24.12(613) H x 3.19(81) D inside the wall, 0.87(22) D outside the wall in(mm) 1.00 (25) Rim with 0.25(6) radius corners in(mm)
Weight:	59 pounds (26.8kg)
Mounting:	Recess mounts, strobe/sounder mounts to standard 4" square box. For surface mount version, order mode CU-8
Communication:	Lighted phone with 12-key pad receives and selectively originates calls
Power Source:	Stations receive power from Command Unit, powered by UPS. UPS requires 120 VAC.
Wiring:	1 twisted, shielded pair per station not to exceed 25 ohms resistance
Lighting:	Strobe is rated at 15 candela, flashes once per second
Environment:	Command Unit is for indoor use, outdoor Area of Rescue Stations are available

Area of Rescue Stations


Surface Mount Station:	Model ETP-100MB is an indoor surface mount Area of Rescue Station
Flush Mount Station:	Model ETP-100EB is an indoor flush mount Area of Rescue Station
Outdoor Station:	Use Models ETP-400 and ETP-SM for an outdoor Area of Rescue Station

Options & Accessories


Polycarbonate Sign:	Model ETP-SIGN is a polycarbonate Area of Rescue sign
Lighted Sign:	Model ETP-SIGN/L is a lighted Area of Rescue sign
Deluxe Lighted Sign:	Model ETP-SIGN/LD is a lighted Area of Rescue sign with battery backup
Mounting Sleeve:	Model MS-400 is a flush mounting sleeve (rough-in box) for ETP-100EB

CU-8R – Area of Rescue Command Unit


Dimensions




Front View



Side View




Bottom View



Top View

Sample Layout



4 Area of Rescue Stations shown. Maximum of 8 per CU-8 system.

Copyright 2009 Talk-A-Phone Co. All rights reserved.

Talk-A-Phone Co. • 7530 North Natchez Avenue • Niles, Illinois 60714-3804
 Phone 773.539.1100 • Fax 773.539.1241 • info@talkaphone.com • www.talkaphone.com
 All prices and specifications are subject to change without notice.
 Talk-A-Phone, Talk-A-Lert, Scream Alert and WEBS are registered trademarks of Talk-A-Phone Co.