


**ETP-100MB – Surface Mounting Emergency Phone**

**Description**

The **ETP-100MB** is an indoor, ADA-compliant hands-free Emergency Phone for use in locations such as: elevators, areas of rescue, stairwells, indoor controlled-access areas, senior citizen housing and correctional facilities.

**Features**

- Cast metal raised letter and Braille signage for ADA compliance
- Vandal resistant stainless steel faceplate and metal button
- Uses regular phone lines or PBX
- Phone line powered: no power supply or battery back-up needed
- Push button once to call, then speak hands-free
- LED indicator for hearing impaired
- Built-in auto-dialer can dial two numbers: if first number doesn't answer or is busy, dials second number
- Auto-answer allows security to monitor and initiate calls with Emergency Phone
- Options available that offer the ability to automatically identify attendant of location of calling phone by recorded message and digital display



**Specifications**

Construction:	12 gauge (2.8mm) #4 brushed stainless steel face plate
Dimensions:	4.81(122) W x 8.19(208) H x 2.5(64) D in(mm)
Weight:	6 lbs. (2.7kg)
Mounting:	Surface mounts
Communication:	2-way hands-free communication
Digit Capacity:	Up to 18 digits, including pauses, for each of two phone numbers
Dialing Speed:	Approximately 10 tones per second
Power Source:	Phone line powered (requires 20mA at 24 v off-hook)
Connection:	Parallel tip and ring connected to RJ11 connector for quick installation
Circuit Protection:	Varistor lightning suppressed and full wave polarity guarded
Programming:	Non-volatile EEPROM programming can be done from any telephone. No battery back-up is needed
"On Time":	Programmable from 1-4270 minutes in 1-minute increments.
Wiring Requirements:	1 twisted-shielded pair


**Options & Accessories**

Voice Location Identifier:	Model <b>ETP-100MBV</b> includes the capability to record a message identifying the location of the call. Message is recorded and duration set during programming.
Auxiliary Input/Outputs:	Add " <b>AUX</b> " to model number. Input allows unit to be activated by any device that creates a contact closure. Two outputs can activate a strobe or light as well as remotely control a door, CCTV or other device.
8-Line Consolidator:	Model <b>EC-8</b> allows connection of up to 8 phones on one phone line while retaining ability to call each phone individually. Can also create a closed system without need for any phone lines.
Scream Detector:	Scream Alert™, model <b>SA-1</b> , automatically activates phone upon hearing a scream (requires <b>AUX</b> option)
Monitoring/Diagnostic Software Package:	Talk-A-Lert®, model <b>ETP-TAL</b> , automatically polls each Emergency Phone, reports incoming calls and keeps permanent records of all events

Copyright 2009 Talk-A-Phone Co. All rights reserved.

# ETP-100MB – Surface Mounting Indoor Emergency Phone

## Dimensions



Copyright 2009 Talk-A-Phone Co. All rights reserved.

Talk-A-Phone Co. • 7530 North Natchez Avenue • Niles, Illinois 60714-3804  
Phone 773.539.1100 • Fax 773.539.1241 • info@talkaphone.com • www.talkaphone.com  
All prices and specifications are subject to change without notice.  
Talk-A-Phone, Talk-A-Lert, Scream Alert and WEBS are registered trademarks of Talk-A-Phone Co.