

**ETP-401 – Single Button Emergency Phone**

**Description**


Model **ETP-401** is an outdoor-rated, ADA-compliant hands-free Emergency Phone for use in locations such as: parking facilities, college campuses, controlled access gates, medical centers and industrial parks.



**Features**

- Cast metal raised letter and Braille signage for ADA compliance
- Vandal resistant stainless steel faceplate and metal button
- Uses regular phone lines or PBX
- Phone line powered: no power supply or battery back-up needed
- Auxiliary input and outputs to integrate with CCTV, Blue Light Strobe, Scream Alert™ and other devices
- Push button once to call, then speak hands-free
- Circuit boards are conformally coated for water protection
- LED indicator for hearing impaired
- Built-in auto-dialer can dial two numbers: if first number doesn't answer or is busy, dials second number.
- Auto-answer allows security to monitor and initiate calls with Emergency Phone
- Options available that offer the ability to automatically identify attendant of location of calling phone by recorded message and digital display

**Specifications**

Construction:	12 gauge (2.8mm) #4 brushed stainless steel faceplate
Dimensions:	6.81(173) W x 9.94(252) H x 2.88(73) D in(mm)
Weight:	8 lbs. (3.6kg)
Operating Temperature:	-4°F to +149°F (-20°C to +65°C)
Mounting:	Surface mounts with rear wire entry
Communication:	2-way hands-free communication
Digit Capacity:	Up to 18 digits, including pauses, for each of two phone numbers
Dialing Speed:	Approximately 10 tones per second
Power Source:	Phone line powered (requires 20mA at 24 v off-hook)
Connection:	Parallel tip and ring connected to RJ11 connector for quick installation
Circuit Protection:	Varistor lightning suppressed and full wave polarity guarded
Programming:	Non-volatile EEPROM programming can be done from any telephone. No battery back-up is needed
"On Time":	Programmable from 1-4270 minutes in 1-minute increments
Wiring Requirements:	1 twisted-shielded pair
Compliance:	CSA Certified to UL Standard 60950 


**Options & Accessories**

Voice Location Identifier:	Model <b>ETP-401V</b> includes the capability to record a message identifying the location of the call. Message is recorded and duration set during programming
"TO CALL" Casting:	Use Model <b>ETP-401C</b> for a button that reads TO CALL instead of <b>EMERGENCY</b>
Mounting Extension:	Use Model <b>ETP-SME</b> to allow easy conduit entry
8-Line Consolidator:	Model <b>EC-8</b> allows connection of up to 8 phones on one phone line while retaining ability to call each phone individually. Can also create a closed system without need for any phone lines
Monitoring/Diagnostic Software Package:	Talk-A-Lert®, model <b>ETP-TAL</b> , automatically polls each Emergency Phone, reports incoming calls and keeps permanent records of all events

Copyright 2009 Talk-A-Phone Co. All rights reserved.

# ETP-401 – Single Button Outdoor Emergency Phone

## Dimensions



Copyright 2009 Talk-A-Phone Co. All rights reserved.

Talk-A-Phone Co. • 7530 North Natchez Avenue • Niles, Illinois 60714-3804  
Phone 773.539.1100 • Fax 773.539.1241 • info@talkaphone.com • www.talkaphone.com  
All prices and specifications are subject to change without notice.  
Talk-A-Phone, Talk-A-Lert, Scream Alert and WEBS are registered trademarks of Talk-A-Phone Co.