Connector Pressing Telecom Pliers.

Designed to crimp telecom-style splice connectors including UG, UR, UB and UY style made by 3M and other manufacturers. Manufactured in accordance with Bell Specifications, these pliers feature a built-in side cutter, coil spring and a built-in stop to prevent damage to connectors.



Technical / Features

- Use for pressing/crimping UR, UY, UG and UB style connectors
- Also compatible with other telecom-style splice connectors
- Built-in side cutter and stop
- Coil spring
- Vinyl handles

Part #	Description
12100C	Connector Pressing Telcom Pliers

Packaging Description	UB 22-26 AWG	UR 19-26 AWG	UY 22-26 AWG
Clamshell – 25 Pieces	18131	18111	18121
Clamshell – 50 Pieces		18112C	
Clamshell – 100 Pieces	18132C		18122C
Box – 100 Pieces*	18130	18110	18120
Jar – 200 Pieces		28110J	

* Bulk quantities available. Contact us for pricing & delivery.

Can Wrench.

For telephone craftwork to connect wires to fuses, tighten nuts on binding post terminals and insert fuses in cable terminals. Double ended 3/8" and 7/16" hex sockets are color coded for quick identification of socket sizes. Design allows use of a wrench for additional torque. Sockets designed with thin walls for access into tight spaces.

Technical / Features

- 3/8" & 7/16" hex nuts
- Access telephone boxes and pedestals
- Tighten nuts on binding post terminals
- Rugged high impact extruded plastic handle
- Manufactured from high carbon tool steel and heat treated for strength and durability

Part #	Description
19059C	Can Wrench

Heavy Duty Cable Tie Gun.

The professional's choice with its robust all steel construction, adjustable tension wheel and automatic cut-off. Trims cable ties flush, eliminating dangerous sharp edges on cable ties. Use with standard and heavy duty cable ties.

Technical / Features

- Maximum capacity of 0.250" width
- Tension adjustment wheel in handle
- Automatic flush cut-off eliminates sharp edges on ties

Part #	Description
10200C	Heavy Duty Cable Tie Gun

Coax Adapters

F Connector Coupler, High Performance F81
Clamshell – 2 pieces **TAD001**

F Female-to-Female Coupler
Clamshell – 2 pieces **18301C**
Bag – 25 pieces **18301**

BNC Female-to-F Female
Clamshell – 2 pieces **18303C**
Bag – 25 pieces **18303**

BNC Female-to-F Male
Clamshell – 2 pieces **18305C**
Bag – 25 pieces **18305**

F Male-to-F Male Splice
Clamshell – 2 pieces **18307C**
Bag – 25 pieces **18307**

BNC Inline Splice Female-to-Female
Clamshell – 2 pieces **18308C**
Bag – 25 pieces **18308**

F Male Terminator 75 ohm
Clamshell – 2 pieces **18306C**
Clamshell – 10 pieces **18309C**
Bag – 25 pieces **18309**

BNC Male-to-F Female
Clamshell – 2 pieces **18310C**
Bag – 25 pieces **18310**

RCA Male-to-BNC Female
Clamshell – 2 pieces **18314C**
Bag – 25 pieces **18314**

Telecom Splicing Connectors.

Utilize an insulation displacement contact (IDC) design for fast, simple, reliable terminations. No wire stripping is required and connectors will accept wire of different gauges. All connectors are gel filled to provide moisture resistance and inhibit corrosion. For use with solid copper conductors only. Typical uses include butt splicing 2 or 3 wires of the same or different gauges. Perfect for pigtail and load coil splice applications.

Technical / Features

Telecom Splicing Connectors UB-Gel Filled

- 26-22 AWG, in-line tap
- Tap directly on to existing wire without interrupting service
- Max insulation OD, .050" (1.27mm)

Telecom Splicing Connectors UR-Gel Filled

- 26-19 AWG, 2 or 3 wire splice
- Use for butt splicing 2 or 3 wires
- Wires can be of different wire gauges
- Max. insulation OD, .066"(1.67mm)

Telecom Splicing Connectors UY-Gel Filled

- 26-22 AWG, 2 wire splice
- Wires can be of different wire gauges
- Max. insulation OD, .060" (1.52mm)

UB

UR

UY

Packaging Description	UB 26-22 AWG	UR 26-19 AWG	UY 26-22 AWG
Clamshell – 25 Pieces	**18131**	**18111**	**18121**
Clamshell –50 Pieces		**18112C**	
Clamshell –100 Pieces	**18132C**		**18122C**
Box – 100 Pieces*	**18130**	**18110**	**18120**
Jar – 200 Pieces		**28110J**	

* Bulk quantities available.
Contact us for pricing & delivery.