THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

CATALOG NUMBER	STRANDED COPPER CONDUCTOR SIZE (AWG)		NO. RIBS	DIMENSIONS - IN [mm]				COLOR CODE	WIRE STRIP LENGTH	INSTALLATION TOOLING PANDUIT DIE PART NO. DIE SET COLOR & INDEX NO. NO. OF CRIMPS ()			
	RUN	TAP		A	Q	T (MAT'L THICKNESS)	V			CT-2001		CT-1700**	CT-920, CT-920CH, CT-2920, CT-930, CT-930CH, CT-940CH*, CT-2940*
CTAPF10-16-C	14 12 10	16-14 16-12 14	0	.41 [10.4]	.13 [3.3]	.06 [1.5]	.19 [4.8]	RED	1/2 [12.7]	----------	CD-2001-8 RED P21 (1)	RED P21 (2)	----------
CTAPF8-12-C	10 8	10 12	0	.67 [17.0]	.19 [4.8]	.07 [1.8]	.26 [6.6]	BLUE	11/16 [17.5]	----------	CD-2001-6 BLUE P24 (1)	BLUE P24 (2)	----------
CTAPF6-12-C	8 6	10-8 12-10	0	.67 [17.0]	.24 [6.1]	.07 [1.8]	.32 [8.1]	GRAY	11/16 [17.5]	----------	CD-2001-4 GRAY P29 (1)	GRAY P29 (2)	----------
CTAPF4-12-C	6 5,4	8-6 12-8	1	1.25 [31.8]	.28 [7.1]	.07 [1.8]	.40 [10.2]	BROWN	1-5/16 [33.3]	CDM-2001-2 BROWN P33M (1)	CD-2001-2 BROWN P33 (2)	BROWN P33 (4)	CDM-920-2 BROWN P33M (1)
CTAPF3-12-C	5,4 3	6-5 12-6	1	1.25 [31.8]	.31 [7.9]	.08 [2.0]	.46 [11.7]	GREEN	1-5/16 [33.3]	CDM-2001-1 GREEN P37M (1)	CD-2001-1 GREEN P37 (2)	GREEN P37 (4)	CDM-920-1 GREEN P37M (1)
CTAPF2-12-C	4 3 2	4 5 12-6	1	1.25 [31.8]	.33 [8.4]	.08 [2.0]	.51 [13.0]	PINK	1-5/16 [33.3]	CDM-2001-1/0 PINK P42M (1)	CD-2001-1/0 PINK P42 (2)	----------	CDM-920-1/0 PINK P42M (1)
CTAPF1-12-C	3 2 1	4-3 5-4 12-5	2	1.82 [46.2]	.40 [10.2]	.08 [2.0]	.57 [14.5]	BLACK	1-7/8 [47.6]	CDM-2001-2/0 BLACK P45M (1)	CD-2001-2/0 BLACK P45 (3)	----------	CDM-920-2/0 BLACK P45M (1)
CTAPF1/0-12-L	2 1 1/0	4-2 4-3 12-4	2	1.82 [46.2]	.42 [10.7]	.09 [2.3]	.63 [16.0]	ORANGE	1-7/8 [47.6]	CDM-2001-3/0 ORANGE P50M (1)	CD-2001-3/0 ORANGE P50 (3)	----------	CDM-920-3/0 ORANGE P50M (1)
CTAPF2/0-12-Q	1 1/0 2/0	2-1 3-2 12-3	2	1.82 [46.2]	.48 [12.2]	.09 [2.3]	.71 [18.0]	PURPLE	1-7/8 [47.6]	----------	CD-2001-4/0 PURPLE P54 (3)	----------	CDM-920-4/0 PURPLE P54M (1)
CTAPF3/0-12-Q	1/0 2/0 3/0	1-1/0 2-1 12-2	2	1.82 [46.2]	.55 [14.0]	.09 [2.3]	.81 [20.6]	YELLOW	1-7/8 [47.6]	----------	CD-2001-250 YELLOW P62 (3)	----------	CDM-920-250 YELLOW P62M (1)





*CT-940CH AND CT-2940 REQUIRE CD-940-DA ADAPTER FOR CDM-920DIES
**CT-1700 CRIMP DIE POCKETS ARE INTEGRATED INTO THE TOOL HEAD

CERTIFIED LISTED

NOTES:

1. MATERIAL: COPPER
2. UL LISTED AND CSA CERTIFIED FOR APPLICATIONS UP TO 600 VOLTS. TEMPERATURE RATING 90° C
3. PACKAGE QTY:
   -C = 100
   -L = 50
   -Q = 25

REV	DATE	BY	CHK	DESCRIPTION	ECN	CUST
05	11/09	JHNU	JHNU	CONVERTED DWG TO SOLIDWORKS		
04	10/02	SAB		REMOVED T&B TOOL INFORMATION & ADDED 2 COLUMNS OF PANDUIT TOOL INFORMATION		
03	6/02	SAB	JAC	REMOVED CT-740 & CT-2001 TOOL COLUMN & ADDED T&B COLUMN		
02	9/01	SAB	RLS	REVISED & REDRAWN, ADDED CTAPF10-16-C		
01	9/97	TM	WJB	REVISED RIBS		

PANDUIT CORP. TINLEY PARK, ILLINOIS

NON-INSULATED THIN-WALL C-TAP CONNECTORS
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCES ARE:
(.X) ± — (.XXX) ± —
(.XX) ± — ANGLES ± —

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION

DRAWN BY EJD
MAT'L: SEE NOTES
DATE
CHK'D
SCALE NONE
DRAWING NO / CAD FILE C41172_05
DWG B SIZE