

ETP-100M – Surface Mounting Emergency Phone

Description

The **ETP-100M** is an indoor hands-free Emergency Phone for use in locations such as: elevators, areas of rescue, stairwells, indoor controlled-access areas, senior citizen housing and correctional facilities.

Features

- Vandal resistant stainless steel faceplate and metal button
- Uses regular phone lines or PBX
- Phone line powered: no power supply or battery back-up needed
- Push button once to call, then speak hands-free
- LED indicator for hearing impaired
- Built-in auto-dialer can dial two numbers: if first number doesn't answer or is busy, dials second number.
- Auto-answer allows security to monitor and initiate calls with Emergency Phone
- Options available that offer the ability to automatically identify attendant of location of calling phone by recorded message and digital display



Specifications

Construction:	22 gauge (0.64mm) #4 brushed stainless steel face plate
Dimensions:	4.81(122) W x 8.81(224) H x 2.5(64) D in(mm)
Weight:	4 lbs. (1.8kg)
Mounting:	Surface mounts
Communication:	2-way hands-free communication
Digit Capacity:	Up to 18 digits, including pauses, for each of two phone numbers
Dialing Speed:	Approximately 10 tones per second
Power Source:	Phone line powered (requires 20mA at 24 v off-hook)
Connection:	Parallel tip and ring connected to RJ11 connector for quick installation
Circuit Protection:	Varistor lightening suppressed and full wave polarity guarded
Programming:	Non-volatile EEPROM programming can be done from any telephone. No battery back-up is needed
"On Time":	Programmable from 1-4270 minutes in 1 minute increments.
Wiring Requirements:	1 twisted-shielded pair


Options & Accessories

ADA Signage:	Self-adhesive raised letter and Braille signage is available as model ETP-MP
Voice Location Identifier:	Model ETP-100MV includes the capability to record a message identifying the location of the call. Message is recorded and duration set during programming.
Auxiliary Input/Outputs:	Add " AUX " to model number. Input allows unit to be activated by any device that creates a contact closure. Two outputs can activate a strobe or light as well as remotely control a door, CCTV or other device.
8-Line Consolidator:	Model EC-8 allows connection of up to 8 phones on one phone line while retaining ability to call each phone individually. Can also create a closed system without need for any phone lines.
Scream Detector:	Scream Alert™, model SA-1 , automatically activates phone upon hearing a scream (requires AUX option)
Monitoring/Diagnostic Software Package:	Talk-A-Lert®, model ETP-TAL , automatically polls each Emergency Phone, reports incoming calls and keeps permanent records of all events

Copyright 2009 Talk-A-Phone Co. All rights reserved.

ETP-100M – Surface Mounting Indoor Emergency Phone

Dimensions



Copyright 2009 Talk-A-Phone Co. All rights reserved.

Talk-A-Phone Co. • 7530 North Natchez Avenue • Niles, Illinois 60714-3804
Phone 773.539.1100 • Fax 773.539.1241 • info@talkaphone.com • www.talkaphone.com
All prices and specifications are subject to change without notice.
Talk-A-Phone, Talk-A-Lert, Scream Alert and WEBS are registered trademarks of Talk-A-Phone Co.