

ETP-401C – Single Button Information Phone

Description


Model **ETP-401C** is an outdoor-rated, ADA-compliant hands-free Emergency Phone for use in locations such as: parking facilities, college campuses, controlled access gates, medical centers and industrial parks.

Features

- Cast metal raised letter and Braille signage for ADA compliance
- Vandal resistant stainless steel faceplate and metal button
- Uses regular phone lines or PBX
- Phone line powered: no power supply or battery back-up needed
- Circuit boards are conformally coated for water protection
- LED indicator for hearing impaired
- Auxiliary input and outputs to integrate with CCTV, Blue Light Strobe, Scream Alert™ and other devices
- Built-in auto-dialer can dial two numbers: if first number doesn't answer or is busy, dials second number.
- Auto-answer allows security to monitor and initiate calls with Emergency Phone
- Options available that offer the ability to automatically identify attendant of location of calling phone by recorded message and digital display



Specifications


| | |
|------------------------|--|
| Construction: | 12 gauge (2.8mm) #4 brushed stainless steel faceplate |
| Dimensions: | 6.81(173) W x 9.94(252) H x 2.88(73) D in(mm) |
| Weight: | 8 lbs. (3.6kg) |
| Operating Temperature: | -4°F to +149°F (-20°C to +65°C) |
| Mounting: | Surface mounts with rear wire entry |
| Communication: | 2-way hands-free communication |
| Digit Capacity: | Up to 18 digits, including pauses, for each of two phone numbers |
| Dialing Speed: | Approximately 10 tones per second |
| Power Source: | Phone line powered (requires 20mA at 24 v off-hook) |
| Connection: | Parallel tip and ring connected to RJ11 connector for quick installation |
| Circuit Protection: | Varistor lightening suppressed and full wave polarity guarded |
| Programming: | Non-volatile EEPROM programming can be done from any telephone. |
| "On Time": | Programmable from 1-4270 minutes in 1-minute increments. |
| Wiring Requirements: | 1 twisted-shielded pair |
| Compliance: | CSA Certified to UL Standard 60950  |

Options & Accessories

| | |
|---|--|
| Voice Location Identifier: | Model ETP-401CV includes the capability to record a message identifying the location of the call. Message is recorded and duration set during programming. |
| Faceplate Camera: | Add "OP3" to model number to add a color pinhole camera mounted discreetly behind the faceplate. Add "OP3BW" for a b/w camera. |
| "EMERGENCY" Casting: | Use Model ETP-401 for a button that reads EMERGENCY instead of TO CALL |
| Mounting Extension: | Use Model ETP-SME to allow easy conduit entry |
| 8-Line Consolidator: | Model EC-8 allows connection of up to 8 phones on one phone line while retaining ability to call each phone individually. Can also create a closed system without need for any phone lines. |
| Monitoring/Diagnostic Software Package: | Talk-A-Lert®, model ETP-TAL , automatically polls each Emergency Phone, reports incoming calls and keeps permanent records of all events |

ETP-401C – Single Button Outdoor Information Phone

Dimensions



Copyright 2009 Talk-A-Phone Co. All rights reserved.

Talk-A-Phone Co. • 7530 North Natchez Avenue • Niles, Illinois 60714-3804
Phone 773.539.1100 • Fax 773.539.1241 • info@talkaphone.com • www.talkaphone.com
All prices and specifications are subject to change without notice.
Talk-A-Phone, Talk-A-Lert, Scream Alert and WEBS are registered trademarks of Talk-A-Phone Co.