

ETP-402C – Dual Button Emergency/Information Phone

Description


Model **ETP-402C** is an outdoor-rated, ADA-compliant hands-free 2-button Emergency/Information Phone for use in locations such as: parking facilities, college campuses, controlled access gates, medical centers and industrial parks.

Features

- Two buttons for both Emergency and non-Emergency calls
- Cast metal raised letter and Braille signage for ADA compliance
- Vandal resistant stainless steel faceplate and metal buttons
- Uses regular phone lines or PBX
- Phone line powered: no power supply or battery back-up needed
- Auxiliary input and outputs to integrate with CCTV, Blue Light Strobe, Scream Alert™ and other devices
- Push button once to call, then speak hands-free
- Circuit boards are conformally coated for water protection
- LED indicator for hearing impaired
- Built-in auto-dialer can dial two numbers per button: if first number doesn't answer or is busy, dials second number.
- Auto-answer allows security to monitor and initiate calls with Emergency Phone
- Options available that offer the ability to automatically identify attendant of location of calling phone by recorded message and digital display



Specifications

| | |
|------------------------|--|
| Construction: | 12 gauge (2.8mm) #4 brushed stainless steel face plate |
| Dimensions: | 6.81(173) W x 9.94(252) H x 2.88(73) D in(mm) |
| Weight: | 8 lbs. (3.6kg) |
| Operating Temperature: | -4°F to +149°F (-20°C to +65°C) |
| Mounting: | Surface mounts with rear wire entry |
| Communication: | 2-way hands-free communication |
| Digit Capacity: | Up to 18 digits, including pauses, for each of two phone numbers |
| Dialing Speed: | Approximately 10 tones per second |
| Power Source: | Phone line powered (requires 20mA at 24 v off-hook) |
| Connection: | Parallel tip and ring connected to RJ11 connector for quick installation |
| Circuit Protection: | Varistor lightning suppressed and full wave polarity guarded |
| Programming: | Non-volatile EEPROM programming can be done from any telephone. No battery back-up is needed |
| "On Time": | Programmable from 1-4270 minutes in 1 minute increments. |
| Wiring Requirements: | 1 twisted-shielded pair |
| Compliance: | CSA Certified to UL Standard 60950  |

Options & Accessories

| | |
|----------------------------|--|
| Voice Location Identifier: | Model ETP-402CV includes the capability to record a message identifying the location of the call. Message is recorded and duration set during programming. |
| "EMERGENCY" Casting: | On Model ETP-402 the top button reads EMERGENCY instead of TO CALL |
| Mounting Extension: | Use Model ETP-SME to allow easy conduit entry |
| 8-Line Consolidator: | Model EC-8 allows connection of up to 8 phones on one phone line while retaining ability to call each phone individually. Can also create a closed system without need for any phone lines. |
| Monitoring/Diagnostic | Talk-A-Lert®, model ETP-TAL , automatically polls each Emergency Phone, reports |

ETP-402C – Dual Button Emergency/Information Phone

Software Package: incoming calls and keeps permanent records of all events

Dimensions

