On Line Catalog



BURNDY Catalog Number	YA6CN
UPC Number	7818101052455
Description	CU HYLUG- 6 STR-1/2-LONG
Status	Active

Web Use
BURNDY Product Line

Dimensional	
Tongue Angle	Straight
Length (in)	2.64
Barrell Style	Chamfered
Bolt Hole Size (in)	0.52
Barrel Type	Long
Thickness	0.12
B Length (in)	1.12
Pad Width (in)	0.83
Strip Length	1-3/16
General	
Number of Holes	1
Product Description	Copper Compression Lug, 1 Hole w/o Inspection Window, #6 AWG, 1/2" Stud, Long Barrel, Tin Plated
Conductor(s)	
Flex (Class G) Size - Range	N/A
Flex (Class H) Size - Range	N/A
Flex (Class I) Size - Range	N/A
Copper Solid Size (Range)	N/A
DLO Size (Range)	N/A
Copper Stranded (Range)	6 AWG
Physical	
Type of Plating	Tin
Bolt Hole Size	1/2
Color Code	Blue
Plated (Yes or No)	Y
Index Number	7
Product Material	Copper
Approvals / Certifications	
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175