4 ST-DUPLEX (EIGHT FIBERS) MULTIMODE ADAPTERS WITH PHOSPHOR-BRONZE ALIGNMENT SLEEVES

OR-OFP-STD08MB | Ortronics

FEATURES & BENEFITS

Ortronics fiber adapter panel allows for flexibility and expansion with an industry accepted style. The adapter panel snaps in for installation and can be removed easily for future changes. The adapter panel is silkscreened for easy port identification

RoHS

- Standard adapter panel is front removable
- Uses plunger/grommet fastener

SPECIFICATIONS

GENERAL INFO

Number Of Ports: 4
Typical Applications: Multimode
Connection Type: ST
Installation Destination: Fiber Cabinets

ASSEMBLY/INSTALLATION INFORMATION

Mounting Hardware Included: Yes

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

DIMENSIONS

Height (Metric): 30 mm
Height (US): 1.19"
Width (Metric): 130 mm

TECHNICAL INFORMATION

Fiber Capacity: 8
Performance Rating: ST
Capacity: Standard Density
Equipment Type: Adapters

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant