



OmniSeal™ Compression Tools & Connectors

- Factory pre-set to work with all IDEAL compression connectors
- Compress F-type, RCA, BNC, Mini and RG-11 Connectors
- Adjustable to fit other manufacturers' connectors - no adapters required
- Connectors designed for use in satellite, cable, CCTV and AV systems



NEW

- RG-6 Plenum
- RG-59 Plenum
- RG-59
- RG-6
- RG-6Q
- RG-11
- MINI



IDEAL DataComm

- CUT
- STRIP
- TERMINATE
- TEST
- CERTIFY



OmniSeal™ Compression Tools and Connectors

OmniSeal™ Pro and Pro XL Universal Compression Tools

The IDEAL OmniSeal™ compression tools offer new additional features and increased connector compatibility in a smaller, more compact tool design to meet the demands of the professional installer. OmniSeal requires no calibration or accessory attachment to terminate IDEAL branded connectors. Most other manufacturers' compression connectors can be terminated with an easy plunger depth adjustment. The simple intuitive design combined with its size and universal connector acceptance makes this the only compression tool needed by professional installers.



**OmniSeal Pro
30-603**



**OmniSeal Pro XL
30-793**

| | BNC | F-Type | RG11 | RCA | Mini Coax |
|-------------------------------|----------------|--------|------|-----|-----------|
| OmniSeal Pro XL 30-793 | ✓ | ✓ | ✓ | ✓ | ✓ |
| OmniSeal Pro 30-603 | (w/adjustment) | ✓ | ✓ | ✓ | ✓ |

| Cat. No. | Description |
|---------------|----------------------------------|
| 30-793 | OmniSeal Pro XL Compression Tool |
| 30-603 | OmniSeal Pro Compression Tool |






RTQ™ Universal Compression Connectors

IDEAL Compression Connectors are manufactured to meet the demands of the satellite and cable TV industry. All series of connectors are permanently connected when terminated with an IDEAL OmniSeal™ Compression Tool. All IDEAL compression connectors require a standard 1/4" x 1/4" strip.

- Connectors to fit RG-59, RG-6, Plenum, RG-11 coaxial cable and mini coax
- Designated RTQ connectors fit Regular (dual shield), Tri and Quad shield cables
- Weatherproof for indoor/outdoor use



| Cat. No. | Description | PKG QTY |
|----------|---|----------|
| 92-610 | RG-59 Reg/Tri/Quad Compression F-Connectors | 50/jar |
| 92-619 | | 1000/box |

| | | |
|--------|--|---|
| 92-654 | RG-6 Reg/Tri/Quad Compression F-Connectors | 4 pack |
| 92-651 | | 10 pack |
| 92-650 | | 50/jar |
| 92-656 | | 100/jar |
| 92-659 | | 1000/box |
| 92-655 | | 1000 bulk (20 bags of 50) |
| 92-660 | | RG-6 Plenum, Dual Shield Compression F-Connectors |
| 92-669 | 1000/box | |

| | | |
|---------|---|---------|
| 89-211 | RG-11, Dual Shield Compression F-Connectors | 10 pack |
| 89-1211 | | 500/box |

| Operation Specifications | |
|------------------------------|--|
| Bandwidth: | 0 MHz - 3 GHz |
| Impedance: | 75 Ohms (nominal) |
| Return Loss: | Minimum -30 dB @ 3 GHz |
| Tightening Torque: | 30 in-lbs. |
| Operating Temperature Range: | -40°F to +140°F |
| Cable Range: | 60% through Quad Shield, PE and PVC jackets |
| Cable Retention: | 40 lbs. minimum |

| Recommended Tools: | |
|----------------------------|--|
| Data T®-Cutter | 45-074 |
| 1/4" - 1/4" Cable Stripper | 45-603, 45-526, 45-321 45-262, 45-282, 45-111 |
| Compression Tool | 30-603, 30-793 |
| F-Connector Tool | 35-046 |



DataComm Coax Products

BNC Compression Connectors

- Single piece design for easy installation
- Nickel plated brass construction
- Color coded by cable series for easy identification
- 3 GHz bandwidth, 75 ohms impedance
- Red band = RG-59; Blue band = RG-6, White band = RG-59 Plenum and Yellow band = RG-6 Plenum



| Cat. No. | Description | QTY |
|----------------|--|-----------------|
| 92-704 | BNC RG-59 Compression Connector | 4 Pack |
| 89-047 | BNC RG-59 Compression Connector | 15 Pack |
| 89-5047 | BNC RG-59 Compression Connector | Jar of 35 |
| 89-1047 | BNC RG-59 Compression Connector | 1,000 (100/bag) |
| 92-705 | BNC RG-6 Compression Connector | 4 Pack |
| 89-048 | BNC RG-6 Compression Connector | 15 Pack |
| 89-5048 | BNC RG-6 Compression Connector | Jar of 35 |
| 89-1048 | BNC RG-6 Compression Connector | 1,000 (100/bag) |
| 89-049 | BNC RG-59 Plenum Compression Connector | 15 Pack |
| 89-5049 | BNC RG-59 Plenum Compression Connector | Jar of 35 |
| 89-1049 | BNC RG-59 Plenum Compression Connector | 1,000 (100/bag) |
| 89-050 | BNC RG-6 Plenum Compression Connector | 15 Pack |
| 89-5050 | BNC RG-6 Plenum Compression Connector | Jar of 35 |
| 89-1050 | BNC RG-6 Plenum Compression Connector | 1,000 (100/bag) |

RCA & Mini Compression F-Connectors

- Constructed of nickel plated brass and gold plated head
- 3 GHz bandwidth, 75 ohms impedance
- Identifying bands included
- Mini connectors fit 23 AWG mini cable



| Cat. No. | Description | QTY |
|--------------------|----------------------------------|----------------------|
| 92-572 | RG-59 RCA Compression Connectors | 4 Pack |
| 89-572 | RG-59 RCA Compression Connectors | 10 Pack (14 bands) |
| 89-570 | RG-59 RCA Compression Connectors | Jar of 35 (50 bands) |
| 92-582 | RG-6 RCA Compression Connectors | 4 Pack |
| 89-582 | RG-6 RCA Compression Connectors | 10 Pack (14 bands) |
| 89-580 | RG-6 RCA Compression Connectors | Jar of 35 (50 bands) |
| 89-014SMRCA | Mini RCA Compression Connector | 10 Pack |



45-074 Data T[®]-Cutter

- Cuts round communication cable and maintains cable geometry for better cable performance
- Steel reinforced center conductor can be trimmed with bolt cutting holes
- Cushioned comfort grip handles
- Locking latch keeps tool closed in pouch



45-603 Coax/UTP Stripper

- Features two active strip cartridges for all RG-6/6Q/59 and UTP cables
- Push on ring for easy cable into connector insertion
- Rotates easily around finger
- No blade depth adjustments required




45-111 RG-11 Stripper

- Provides a 1/4" x 1/4" strip for RG11 cable
- Adjustable stripper for mini coax cable



45-321 Cable/Satellite/CCTV Coax Stripper

- Designed for fast and easy 1/4" x 1/4" strip lengths
- Blades auto-adjust to different diameter coax cables
- Spinner ring for fast stripping
- Strips RG-6/6Q/59 coax cable



35-046 Connector Tool

- Works on hex style F and BNC connectors
- Makes attaching and detaching connectors to equipment easier
- Aids in installing CATV connectors
- Comfort grip handle



45-526 Coax Cable Stripper

- Provides a 1/4" x 1/4" strip for RG-6/6Q/59 coax cable
- Adjustable stripper for coax cable

IDEAL INDUSTRIES, INC.

Becker Place, Sycamore, IL 60178, USA / 815-895-5181 • 800-435-0705 in USA

International offices:

Australia • Brazil • Canada • China • Germany • Mexico • UK

For complete sales office contact information, visit us at:

www.idealindustries.com