Retail Light Box

High output retail spotlights

- Highly efficient, up to 117 lumens per circuit Watt
- Multi pivot positioning
- Lifelong consistent colour temperature and rendering
- Available in 15°, 24° and 36° beam angles
- Produced to order, contact JCC customer services on **01243 838999**

NEW — New product for 2018

5 year ext. warranty*

15°/24°/36° beam angle options

Produced to order call 01243 838999

JC**66024WH**

JC**66024BLK**

Classification

Class 2
IP20 | 240V

LED

3000K | CRI: Ra (80)
4000K | CRI: Ra (80)

Finishes

Black (**BLK**), White (**WH**)

Construction

Body: Aluminium
Lens: Polycarbonate

Installation

Cut out: 310 x 160mm

JC66021 / JC66024 / JC66022 / JC66025 / JC66023 / JC66026



All data sheets and installation sheets available at jcc.co.uk

Code	Description	Col temp.	Dim.	Watt	Lumens	LpcW
JC**66021**	Retail Light Box Twin 15°	3000K	No	70W	7680	110
JC**66024**	Retail Light Box Twin 15°	4000K	No	70W	8200	117
JC**66022**	Retail Light Box Twin 24°	3000K	No	70W	7680	110
JC**66025**	Retail Light Box Twin 24°	4000K	No	70W	8200	117
JC**66023**	Retail Light Box Twin 36°	3000K	No	70W	7680	110
JC**66026**	Retail Light Box Twin 36°	4000K	No	70W	8200	117

Products available to order, contact JCC customer services on **01243 838999.**

For Black add **BLK** suffix, for White add **WH** suffix.

*Requires online registration.