Starspot™ 600

Dimmable LED spotlights

- Exceeds 50W halogen light output
- Triac dimmable as standard
- 36° beam angle

5 year ext. warranty*

36° beam angle

Dimmable as standard

JC**14222WH**

JC**14222BLK**

Classification

Class 1
IP20 | 240V

LED

3000K | CRI: Ra (85)
4000K | CRI: Ra (85)

Finishes

Black (**BLK**), White (**WH**)

Construction

Body: Aluminium
Lens: Polycarbonate

Installation

Method of fix: Fixed to Single Circuit Track or Three Circuit with JC**88118**

Code	Description	Col temp.	Dim.	Watt	Lumens	LpcW
JC**14222**	Starspot 600	3000K	Yes	7W	580	83
JC**14223**	Starspot 600	4000K	Yes	7W	600	86

For Black add **BLK** suffix, for White add **WH** suffix.

JC14222 / JC14223



*Requires online registration.

All data sheets and installation sheets available at jcc.co.uk