Base/plinth system VX



Base/plinth trim panels, sides

Sheet steel
for base/plinth VX
To finish off a base/plinth unit at the sides and for additional stabilisation or for the interior configuration of bayed base/plinths. One 200 mm high or two 100 mm high trim panels may optionally be fitted on 200 mm high base/plinths.

Material:
– Sheet steel

Colour:
– RAL 9005

Supply includes:
– 2 base/plinth trim panels
– Assembly parts

100 mm high

For enclosure depth mm	Model No.
300	**8640.030**
400	**8640.031**
500	**8640.032**
600	**8640.033**
800	**8640.034**
1000	**8640.035**
1200	**8640.036**

200 mm high

For enclosure depth mm	Model No.
300	**8640.040**
400	**8640.041**
500	**8640.042**
600	**8640.043**
800	**8640.044**
1000	**8640.045**
1200	**8640.046**

Accessories:

– Base/plinth installation bracket, see page 885

Possible alternative:

– Base/plinth trim panels with brush strip, see page 882
– Base/plinth trim panels, vented, see page 883



Base/plinth trim panels with brush strip

Sheet steel
for base/plinth VX
For cable entry in the base/plinth. With a base/plinth height of 200 mm, one or two trim panels with brush strips may optionally be used. Thanks to the complete symmetry of the base/plinth system VX, the trim panels with brush strip may either be fitted at the front, rear or side on the base/plinth corner piece.

Material:
– Base/plinth trim panels: Sheet steel
– Brush strip: Plastic, self-extinguishing

Colour:
– RAL 9005

Supply includes:
– 2 base/plinth trim panels with brush strip
– Assembly parts

For enclosure width/depth mm	Model No.
600	**8620.092**
800	**8620.093**
1000	**8620.094**
1200	**8620.095**