


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT
PRVF12	35.0 LBS/EACH (15.9 kg/EACH)

NOTES:

- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
- COMPONENTS: (1) 12" VERTICAL MANAGER
(1) HARDWARE KIT
(4) MOLDED FRONT SPOOLS (P/N: PRSP7)
- CAN BE USED WITH ANY 19 OR 23 INCH EIA STANDARD RACK.
- 12" DOOR SOLD SEPARATELY (P/N: PRD12)
- 5" REAR MOUNTING SPOOLS SOLD SEPARATELY (P/N: PRSP5)
- SPOOLS HAVE MULTIPLE MOUNTING POSITIONS TO ACCOMMODATE CABLE SLACK.
- DIMENSIONS IN PARENTHESES ARE METRIC.
- ALL DIMENSIONS ARE REFERENCE ONLY.

MODEL FILENAME	V10179AK/12.PRT
CAD FILENAME/LAYERS	V10179AK_DC/12A.PRT
PANDUIT CORP. TINLEY PARK, ILLINOIS	
12" VERTICAL MANAGER FRONT ONLY (PRVF12) CUSTOMER DRAWING	

12A	10-7-11	BAME		UPDATED VIEWS	10179-33		CMK			UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
11A	1-24-11	BAME	NAGL	REMOVED TOLERANCES CHANGED DOOR BRACKET DESIGN	10179-33		CMK						
01	12-14-07	BAME	NAGL	CHANGED FINGER DESIGN	10179-33		CMK			DRAWN BY JDWE	MAT'L: BACKBONE - STEEL SPOOLS - POLYCARBONATE FINGERS - ABS	SCALE NONE	
R	5-17-04	JDWE	MAV	RELEASE TO PRODUCTION	10179-33		MJM			DATE 5-17-04		DRAWING NO. 10179-33	DWG A SIZE
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH	CHK'D MAV			