







THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



- TOP AND BOTTOM -




- SIDES -



NOTES:

1. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
2. DIMENSIONS IN PARENTHESES ARE IN METRIC.
3. PART INCLUDES:
2- CEILING BRACKET (TOP & BOTTOM)
2- CEILING BRACKET (SIDES)
16- #6-32 MOUNTING SCREW
4. DESIGNED FOR USE WITH THE FOLLOWING WIRELESS ACCESS POINT ENCLOSURES: PZWIF1DCB, PZWIF1EN, PZWIF1EA, PZWIF1EH, AND PZWIF1ENA.
5. MATERIAL: ALUMINUM; POWDER COATED WHITE.

PANDUIT P/N	WEIGHT
PZWIF1DCB	2.12 LB/EACH SET (961.6 g/EACH SET)



MODEL FILENAME	V10311BT/02.prt	SIZE	A
DRAWING FILENAME	V10311BT_DC/02A.prt		
PANZONE™ WIRELESS ACCESS POINT ENCLOSURE CEILING BRACKETS (PZWIF1DCB) CUSTOMER DRAWING			
 PANDUIT ™ CORP. TINLEY PARK, ILL 60477		I.I. NUMBER	N/A
		PRODUCT SPEC	N/A
 THIRD ANGLE PROJECTION	ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ± .XXX (.XX) ± .031(.8) ANGLES ±	WORK INSTRUCTION	N/A
		SCALE	NONE
DRAWN BY	Rey B	MATERIAL	PZWIF1DCB
DATE	8-23-05		
CHK'D	RDC		
		PART NO.	PZWIF1DCB
		DRAWING NO.	10311-17

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
O2A	3-20-08	RYB		A. WAS .75; B. WAS .81; C. WAS 13.62; D. WAS .80	10311-17				
O1	3-11-08	BAME		ADDED OFFSET MOUNT UPDATED NOTE 4 TO INCLUDE ALL ENCLOSURES FOR WHICH BRACKET IS DESIGNED.	10311-17				
OO	8-23-05	RYB	RDC	RELEASED TO PRODUCTION	10311-17		BAS		