

# Product Cut Sheet


## STANDARD RACK, 6"D (150 mm)

Features 6"D (150 mm) upright mounting channels for MDF, IDF and other high-capacity distribution frame applications. The additional rack depth provides extra room for high-density equipment and cable needs.

- High strength aluminum construction
- Supplied with (2) top angles for additional strength
- EIA-310-D Standard Universal 5/8"-5/8"-1/2" (5.9 mm - 5.9 mm - 2.7 mm) alternating hole pattern offers greater mounting flexibility and is fully compatible with conventional wide 1 1/4"-1/2" (3.8 mm - 2.7 mm) alternating hole patterns
- Rack-mount units (U) marks simplify equipment installation
- High-strength, roll-formed threaded mounting holes
- Ships unassembled and individually packaged
- Includes assembly hardware and (50) pilot point #12-24 mounting screws with combination Phillips/Straight heads
- Weight capacity 1000 lb (453.6 kg), weight must be evenly distributed and rack must be properly secured to the floor.
- 19"W and 23"W Racks are UL and cUL Listed



Rack Dimensions			
Dimension	19"W EIA Rack	23"W Rack	35"W Rack
A	17.79" (451.9 mm)	21.79" (554.5 mm)	33.79" (858.3 mm)
B	18.32" (465.2 mm)	22.32" (566.9 mm)	34.32" (871.7 mm)
C	20.32" (516.1 mm)	24.32" (617.7 mm)	36.32" (922.5 mm)



The 6"D (150 mm) Standard Rack is the high-capacity frame that is designed for use with cabling sections and is the basic frame around which the XLBET/MDF frames are developed. P/N 66363-X03 shown.

Part Number	Description	Shipping Weight
66353-X03	7'H (2.1 m) x 19"W, 45U	38 lb (17.2 kg)
66383-X03	7'H (2.1 m) x 23"W, 45U	42 lb (19.1 kg)
66363-X03	7'H (2.1 m) x 35"W, 45U	52 lb (23.6 kg)

X=color; 1=Gray, 2=White, 5=Clear, 7=Black

800-834-4969 in U.S. & Canada • [www.chatsworth.com](http://www.chatsworth.com)



CHATSWORTH PRODUCTS, INC.

©2011 Chatsworth Products, Inc. All rights reserved. CPI, CPI Passive Cooling, MegaFrame, Saf-T-Grip, Seismic Frame, SlimFrame, TeraFrame, GlobalFrame, Cube-IT Plus, Evolution, OnTrac, QuadraRack and Velocity are federally registered trademarks of Chatsworth Products, Inc. Simply Efficient is a trademark of Chatsworth Products, Inc. All other trademarks belong to their respective companies. Rev. 4 11/11