




△C

PANDUIT PART NUMBER	WEIGHT
FR12TB12 FR12TB12M	2.71 LB/EACH (1230g/EACH)



1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE PACKAGE QUANTITY.
2. THE FIBERRUNNER 12x4 QUIKLOCK TRAPEZE BRACKET IS USED TO SUPPORT THE FIBERRUNNER 12x4 CABLE ROUTING SYSTEM BETWEEN TWO (2) SECTIONS OF NEW OR EXISTING 1/2" (M12) THREADED ROD THAT ARE 18" (457.2) - 20" (508) APART.
3. THE FIBERRUNNER 12x4 QUIKLOCK TRAPEZE BRACKET INCLUDES:
ONE (1) BRACKET ASSEMBLY,
FOUR (4) 1/2 HELICAL SPRING LOCKWASHERS,
FOUR (4) 1/2-13 HEAVY HEX NUTS (FR12TB12 ONLY),
FOUR (4) M12x1.75 HEX NUTS (FR12TB12M ONLY).
ONE (1) 1/4-20 T-BOLT,
ONE (1) 1/4-20 HEX KEPS NUT
4. FINISH COLOR: BLACK (EXCEPT FOR HARDWARE).
5. DIMENSIONS IN PARENTHESES ARE IN METRIC.



CAD_FILENAME/LAYERS



\\FR12TB12.pdf

2	7-31-06	DTP	RN	H. REVISED PART WEIGHT. G. REVISED GENERAL NOTE #3.	38022-49	RN	RN			
-	-----	---	---	F. REMOVED ALL REFERENCES TO PART NUMBER FR12TB58M.	-----	--	--			
-	-----	---	---	E. REVISED ENTIRE DRAWING TO INCLUDE FR12TB12.	-----	--	--			
-	-----	---	---	D. REVISED GENERAL NOTES. C. REVISED CHART.	-----	--	--			
1	1-12-05	MSO	RPA	B. REVISED DRAWING TITLE. A. REVISED CAD FILENAME.	38022-49	RN	RN			
R	10-2-01	JHNU	RPA	RELEASED TO PRODUCTION	38022-49	HIW	HIW			
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	GBM	

PANDUIT CORP. TINLEY PARK, ILLINOIS

FIBERRUNNER 12x4 QUIKLOCK TRAPEZE
BRACKET - 1/2" (M12) THREADED ROD
(FR12TB12, FR12TB12M)
CUSTOMER DRAWING



UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:

(.X) ±	(.XXX) ±
(.XX) ± .03 (.8)	ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN IN
INCHES, THIRD ANGLE PROJECTION.

DRAWN BY JHNU

DATE	10-2-01
------	---------

CHK'D	RPA
-------	-----

MAT'L:	
--------	--

STEEL

SCALE	NONE
-------	------

DRAWING NO.

38022 - 49

DWG

A

SIZE