


PoE Tester

PowerDsine Power over Ethernet Tester

Check your RJ-45 outlet for power using the PowerDsine PoE Tester

The Power over Ethernet (PoE) Tester, connected to an RJ-45 outlet, tests the cabling infrastructure for the presence of power, either IEEE802.3af standard-compliant or pre-standard. The PoE Tester identifies the existence and type of Power Sourcing Equipment (either Endspan or Midspan) in your network.

Identify the Power Source:



Features

- Tests RJ-45 outlet for Power over Ethernet existence
- Indicates the type of power source
- Detects:
 - ✓ IEEE 802.3af midspans and switches
 - ✓ Cisco pre-standard in-line switches
 - ✓ High Power midspans
- Compact design specifically tailored for system integrators and installers
- Plug and play, simple to use



The Power over Ethernet Pioneers

PoE Tester

PowerDsine Power over Ethernet (PoE) Tester

Identify the Power Source:

Midspan LED	Endspan LED	Indication
		No power indication
		Standard 802.3af Midspan*
* Few PoE switches are designed to transmit power on the spare pairs. In these cases, the Midspan LED will be illuminated.		
		Standard 802.3af Switch
		Cisco Non-standard Switch (Blinks every 7-9 Sec)
		PowerDsine High Power Midspan

Ordering Information

Order Number	Description
PD-TESTER	Power over Ethernet Tester for RJ-45 Outlet

Specifications:

Input	RJ-45 connector Category 5/5e/6 cable with RJ-45 connectors
Dimensions	(H)0.87x(W)0.94x(D)2.99 in (H)22x(W)24x(D)76 mm
Weight	15 g
Indicators	Midspan LED display (Blue) Endspan LED display (Blue)
Environmental Conditions	Operating Ambient Temperature: 32° to 104°F (0 to 40°C) Operating Humidity: Max. 90%, non-condensing Storage Temperature: -4° to 158°F (-20° to 70°C) Storage Humidity: Max. 95%, non-condensing Operating Altitude: -1000 to 10,000 ft. (-304.8 to 3048 m)
Regulatory	Compliance CE



www.powerdsine.com

International Headquarters

PowerDsine Ltd.
1 Hanagar St.,
P.O.Box 7220
Hod Hasharon 45421
Israel
Tel: +972-9-7755100
Fax: +972-9-7755111
sales@powerdsine.com

North America

PowerDsine, Inc.
1865 New Highway
Farmingdale, NY 11735
USA
Tel: +1-631-756-4680
Fax: +1-631-756-4691
sales@powerdsineusa.com

Europe

PowerDsine UK
Lakeside House
1 Furzeground Way
Stockley Park, Uxbridge
UB11 1BD, United Kingdom
Tel: +44 (0) 208 622 3107
Fax: +44 (0) 208 622 3200
uk@powerdsine.com